# **ARG8PV-FS24LSTACKMED2**



73.5" x 23.38" x 24.38" (H x W x D)

Stacked combination of ARG8PV all-refrigerator and FS24LMED2 compact manual defrost all-freezer for vaccine storage

#### **Highlights:**

Independent refrigerator and freezer storage in one slimfitting footprint for space-challenged facilities

Intelligent microprocessor digital temperature controller for optimum temperature management

Improved temperature accuracy with a separate temperature probe for continuous product readout to simulate stored product temperature

#### **Product Features:**

Allows you to create a full refrigerator-freezer with independent controls in a slim-fitting footprint
Unit ships in three boxes for customer to install the StackRack on the bottom refrigerator/freezer and place and secure the other unit on top
Designed and purpose-built for pharmacy, medication, and vaccine applications to support meeting CDC/VFC guidelines
The published temperature variation is derived from the maximum deviation of an NTC sensor in a 1 oz. vial located nearest the chamber geometric center during a 24 hour test period
Intuitive controls let you adjust the interior temperature between +2 to +8°C (refrigerator) and -20° to -15°C (freezer)
Visual and audible alarms alert if the interior temperature rises or falls out of set range
Electronic controller is equipped with a volt-free contact for alarm forwarding to an external remote system (contacts located in the external rear of the unit)
Adjustable cycle defrost operation ensures the unit avoid temperature spikes and ice buildup

## accuc@ld

### ARG8PV-FS24LSTACKMED2 Specifications:

Overview	
Height of Cabinet	73.5" (187 cm)
Width	23.38" (59 cm)
Width with Door Open	23.88" (61 cm)
Depth	24.38" (62 cm)
Depth with Handle	26.13" (66 cm)
Depth with door at 90°	46.5" (118 cm)
Capacity	9.4 cu.ft. (266 L)
Door	Glass
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Interior Light	Yes
Refrigerator - Interior Height	41.25" (105 cm)
Refrigerator - Interior Width	20.0" (51 cm)
Refrigerator - Interior Depth	17.0" (43 cm)
Refrigerator - Capacity	8.0 cu.ft
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	7
Refrigerator - Temperature Range	2 to 8°C
Refrigerator - Refrigerant Type	R600a
Refrigerator - Refrigerant Amount	1.73 oz.
Freezer - Interior Height	14.38" (37 cm)
Freezer - Interior Width	13.5" (34 cm)
Freezer - Interior Depth	13.25" (34 cm)
Freezer - Capacity	1.4 cu.ft
Freezer - Shelf Type	Wire
Freezer - Shelf Qty	1
Thermostat Type	Digital

Fan Type	Interior
Freezer - Temperature Range	-20° to -15°C
Freezer - Refrigerant Type	R134a
Freezer - Refrigerant Amount	1.5 oz.

