accucold

ARS6PV-VT65MLSTACKMED2



68" x 23.63" x 24.38" (H x W x D)

Stacked combination of ARS6PV all-refrigerator with antimicrobial silver-ion handle and VT65MLBIMED2 manual defrost all-freezer for vaccine storage

Highlights:

Independent refrigerator and freezer storage in one slimfitting footprint for space-challenged facilities

ARS6PV refrigerator comes with a factory-installed powder-coated handle with naturally occurring silver ions to help reduce germ spread

Intelligent microprocessor digital temperature controller for optimum temperature management

Product Features:

Space-saving design	Allows you to create a full refrigerator-freezer with independent controls in a slim-fitting footprint	
Easy assembly	Unit ships in three boxes for customer to install the StackRack on the bottom refrigerator/freezer and place and secure the other unit on top	
Purpose-built design	Designed and purpose-built for pharmacy, medication, and vaccine applications to support meeting CDC/VFC guidelines	
+/-1ºC Variation (refrigerator)	The published temperature variation is derived from the maximum deviation of an NTC sensor in a 1 oz. vial located nearest the chamber geometric center during a 24 hour test period	
Antimicrobial silver ion-coated handle (refrigerator)	Powder-coated handle with naturally occurring silver ions to help reduce the spread of germs	
Adjustable temperature	Intuitive controls let you adjust the interior temperature between +2 to +8 $^{\circ}$ C (refrigerator) and -20 $^{\circ}$ to -15 $^{\circ}$ C (freezer)	
Temperature alarms	Visual and audible alarms alert if the interior temperature rises or falls out of set range	
Remote alarm contacts (refrigerator)	Electronic controller is equipped with a volt-free contact for alarm forwarding to an external remote system (contacts located in the external rear of the unit)	
Automatical at material with red weat of the charge of the	ISA diwstable cycle deformed for the second state of th	

accuceld

ARS6PV-VT65MLSTACKMED2 Specifications:

Overview	
Height of Cabinet	68.0" (173 cm)
Width	23.63" (60 cm)
Depth	24.38" (62 cm)
Depth with Handle	26.13" (66 cm)
Capacity	9.2 cu.ft. (261 L)
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Interior Light	Yes
Refrigerator - Interior Height	24.5" (62 cm)
Refrigerator - Interior Width	20.0" (51 cm)
Refrigerator - Interior Depth	17.0" (43 cm)
Refrigerator - Capacity	6.0 cu.ft
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	4
Refrigerator - Temperature Range	2 to 8ºC
Refrigerator - Refrigerant Type	R600a
Refrigerator - Refrigerant Amount	1.66 oz.
Freezer - Interior Height	24.25" (62 cm)
Freezer - Interior Width	17.63" (45 cm)
Freezer - Interior Depth	17.0" (43 cm)
Freezer - Capacity	3.2 cu.ft
Thermostat Type	Digital
Fan Type	Interior
Freezer - Temperature Range	-12º to -25ºC
Freezer - Refrigerant Type	R134a

Freezer - Refrigerant Amount	
	Presented P 11

