

# ARG6PV-VT65MLSTACKMED2



68" x 23.63" x 24.38" (H x W x D)

Stacked combination of ARG6PV all-refrigerator and VT65MLBIMED2 manual defrost all-freezer for vaccine storage, with antimicrobial silver ion handle

## Highlights:

Independent refrigerator and freezer storage in one slim-fitting footprint for space-challenged facilities

Intelligent microprocessor digital temperature controller for optimum temperature management

Powder-coated handle with naturally occurring silver ions to help reduce germ spread

## Product Features:

Space-saving design	Allows you to create a full refrigerator-freezer with independent controls in a slim-fitting footprint
Easy assembly	Unit ships in three boxes for customer to install the StackRack on the bottom refrigerator/freezer and place and secure the other unit on top
Antimicrobial silver ion-coated handle	Powder-coated handle with naturally occurring silver ions to help reduce the spread of germs
Purpose-built design	Designed and purpose-built for pharmacy, medication, and vaccine applications to support meeting CDC/VFC guidelines
+/-1°C Variation (refrigerator)	The published temperature variation is derived from the maximum deviation of an NTC sensor in a 1 oz. vial located nearest the chamber geometric center during a 24 hour test period
Adjustable temperature	Intuitive controls let you adjust the interior temperature between +2 to +8°C (refrigerator) and -20° to -15°C (freezer)
Temperature alarms	Visual and audible alarms alert if the interior temperature rises or falls out of set range
Remote alarm contacts (refrigerator)	Electronic controller is equipped with a volt-free contact for alarm forwarding to an external remote system (contacts located in the external rear of the unit)
Automatic defrost with adjustable cycle	Adjustable cycle defrost operation ensures the unit avoid temperature spikes and ice buildup

## ARG6PV-VT65MLSTACKMED2 Specifications:

Overview	
Height of Cabinet	68.0" (173 cm)
Width	23.63" (60 cm)
Depth	24.38" (62 cm)
Depth with Handle	26.13" (66 cm)
Capacity	9.2 cu.ft. (261 L)
Door	Glass
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Interior Light	Yes
Refrigerator - Interior Height	24.5" (62 cm)
Refrigerator - Interior Width	20.0" (51 cm)
Refrigerator - Interior Depth	17.0" (43 cm)
Refrigerator - Capacity	6.0 cu.ft
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	4
Refrigerator - Temperature Range	2 to 8°C
Refrigerator - Refrigerant Type	R600a
Refrigerator - Refrigerant Amount	1.66 oz.
Freezer - Interior Height	24.25" (62 cm)
Freezer - Interior Width	17.63" (45 cm)
Freezer - Interior Depth	17.0" (43 cm)
Freezer - Capacity	3.2 cu.ft
Thermostat Type	Digital
Fan Type	Interior
Freezer - Temperature Range	-12° to -25°C
Freezer - Refrigerant Type	R134a

Freezer - Refrigerant Amount

