# TIMMUZ

### **MB12B**



20.25" x 15.88" x 17.25" (H x W x D)

Compact minibar in black with front lock and reversible door

### **Highlights:**

Compact size is ideal for use in hotels and suites

Laboratory-tested for quiet operation of 34.4 decibels

Compressor-based cooling system keeps stored items cold

#### **Product Features:**

Compact dimensions	Slim fit offers the ideal choice for hotel rooms and other settings with limited counter and cabinet space	
Digital controls	Easy temperature management with a digital control panel that lets you choose between six temperature levels at the touch of a button	
Compressor-based cooling system	True refrigeration system that keeps stored items cold	
Quiet operation	Runs at just 34.4 dB for a quiet performance that won't disturb your guests	
Factory installed lock	Front lock offers convenient security, with two keys included	
Reversible door	User-reversible door swing for added flexibility	
Adjustable shelving	Attractive plastic shelf included, with seven glide positions to allow you to accommodate a range of sizes	
Door storage	Two door racks are perfect for keeping smaller bottles and condiments in easy reach	
Interior LED light	Automatically illuminates when the door is opened for an attractive, energy efficient view	



# TIMMUZ

### **MB12B Specifications:**

Overview			
Height of Cabinet	20.25" (51 cm)		
Width	15.88" (40 cm)		
Width with Door Open	16.13" (41 cm)		
Depth	17.25" (44 cm)		
Depth with door at 90°	31.5" (80 cm)		
Capacity	0.7 cu.ft. (20 L)		
Defrost Type	Automatic		
Door	Black		
Cabinet	Black		
US Electrical Safety	ETL		
Canadian Electrical Safety	ETL-C		
Energy Usage/Year	148.0kWh/year		
Amps	0.4		
Voltage/Frequency	115 V AC/60 Hz		
Weight	36.0 lbs. (16 kg)		
Shipping Weight	40.0 lbs. (18 kg)		
Estimated Time to Ship	Next day shipping		
Parts & Labor Warranty	1 Year		
Compressor Warranty	5 Years		
Refrigerator Features			
Door Swing	RHD		
Reversible	Yes		
Shelf Type	Plastic		
Shelf Qty	1		
Full Door Shelf Qty	2		
Adjustable Shelves	Yes		
Thermostat Type	Digital		
Refrigerant Type	R600a		
Refrigerant Amount	0.85oz.		
High Side PSI	106.0		
Low Side PSI	55.0		
Interior Light	Yes		
Dimensions			
Interior Height	15.88" (40 cm)		
Interior Width	12.25" (31 cm)		
Interior Depth	8.5" (22 cm)		
Compressor Step Height	7.5" (19 cm)		

Compressor Step Width	12.25" (31 cm)
Compressor Step Depth	1.5" (4 cm)



