SUMMIT

MB27G



22.25" x 15.88" x 19" (H x W x D)

Compact minibar with reversible glass door, front lock, and black cabinet

Highlights:

Compact size is ideal for use in hotels and suites

Quiet compressor-based cooling system keeps stored items cold

Glass door provides a full display of stored items

Product Features:

Compact dimensions	Slim fit offers the ideal choice for hotel rooms and other settings with limited counter and cabinet space	
Double pane tempered glass door	Ideal for displaying stored contents to your guests	
Digital controls	Easy temperature management with a digital control panel that lets you choose between six temperature levels at the touch of a bottom	
Compressor-based cooling system	Quiet operation with a true refrigeration system that keeps stored items cold	
Quiet operation	Runs at just 34.5 dB for a quiet performance that won't disturb your guests	
Factory installed lock	Front lock offers convenient security, with two keys included	
Reversible door	User-reversible door swing for added flexibility	
Adjustable shelving	Two plastic shelves included, with ten glide positions to allow you to accommodate a range of sizes	
Interior LED light	Automatically illuminates when the door is opened for an attractive, energy efficient view	







MB27G Specifications:

Overview		
Height of Cabinet	22.25" (57 cm)	
Width	15.88" (40 cm)	
Depth	19.0" (48 cm)	
Depth with door at 90°	34.0" (86 cm)	
Capacity	1.2 cu.ft. (34 L)	
Defrost Type	Automatic	
Door	Glass	
Cabinet	Black	
US Electrical Safety	ETL	
Canadian Electrical Safety	ETL-C	
Energy Usage/Year	226.0kWh/year	
Amps	0.4	
Voltage/Frequency	115 V AC/60 Hz	
Weight	55.11 lbs. (25 kg)	
Shipping Weight	60.11 lbs. (27 kg)	
Estimated Time to Ship	Next day shipping	
Parts & Labor Warranty	1 Year	
Compressor Warranty	5 Years	
Refrigerator Features		
Door Swing	RHD	
Reversible	Yes	
Shelf Type	Plastic	
Shelf Qty	2	
Adjustable Shelves	Yes	
Thermostat Type	Digital	
Fan Type	Interior	
Refrigerant Type	R600a	
Refrigerant Amount	0.85oz.	
High Side PSI	106.0	
Low Side PSI	55.0	
Interior Light	Yes	
Dimensions		
Interior Height	17.88" (45 cm)	
Interior Width	12.25" (31 cm)	
Interior Depth	9.75" (25 cm)	

