

BIM68OSGDR



33.63" x 14.88" x 22.63" (H x W x D)

15" wide 62 lb. built-in undercounter commercially listed indoor/outdoor clear icemaker with gravity drain and complete stainless steel exterior finish

Highlights:

Weatherproof construction for use in the outdoors

Commercially approved to NSF-12 standards

Produces up to 62 lbs. of gourmet style clear ice cubes in a 24 hour cycle

Product Features:

Commercially approved	ETL-S listed to NSF-12 commercial standards for use in foodservice settings
Weatherproof design	Durable construction for safe installation in outdoor kitchens
62 lb. production capacity	Can make up to 62 lbs. in a day cycle, producing 24 cubes in a 30 minute span
Built-in capable	Make the best use of space by installing your icemaker under the counter and flush with other cabinets
Stainless steel wrapped exterior	Door and cabinet are fully wrapped in 304 grade stainless steel for lasting elegance
Professional handle	Horizontally mounted towel bar style handle in stainless steel
Clear ice cube production	Gourmet style rounded dice-style ice cubes
Frost-free operation	No-frost operation for minimum user maintenance
Gravity drain setup	Requires connection to gravity drain



BIM68OSGDR Specifications:

Overview	
Height of Cabinet	33.5" (85 cm)
Height to Hinge Cap	33.63" (85 cm)
Width	14.88" (38 cm)
Depth	22.63" (57 cm)
Depth with Handle	24.5" (62 cm)
Depth with door at 90°	37.25" (95 cm)
Capacity	0.98 cu.ft. (28 L)
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	4.0
Voltage/Frequency	115 V AC/60 Hz
Weight	105.0 lbs. (48 kg)
Shipping Weight	110.0 lbs. (50 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101057088
Icemaker	
Door Swing	RHD
Reversible	Yes
Daily Ice Production	62.0 lbs. (28 kg)
Ice Storage Capacity	26.0 lbs. (12 kg)
Ice Shape	Dice
Size of Cube	1 1/4" H x 1 1/8" W x 1 1/8" D
Number of Ice Cube Sizes	1
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	7.4 oz.
High Side PSI	210.0
Low Side PSI	105.0
Interior Height	12.75" (32 cm)

Interior Width	12.75"
Interior Depth	9.25"
Level Legs	

