

# BIM44GADA



32.56" x 14.5" x 23.5" (H x W x D)

ADA compliant NSF-listed auto defrost clear icemaker with internal pump for built-in or freestanding use under counters

### Highlights:

- Commercial ENERGY STAR certification
- 32 3/8" height fits under lower ADA compliant counters
- Automatic defrost saves on user maintenance

### Product Features:

ADA compliant	32 3/8" height fits under lower ADA compliant counters
ENERGY STAR certified commercial performance	Efficient performance for commercial use
Commercially approved	NSF listed for use in commercial establishments
Built-in pump	Internal pump allows more flexibility in placing the unit
Automatic defrost	Simplify appliance care by letting your icemaker defrost itself
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes; Unit ships LHD but can be reversed in our factory or by the user
Built-in capable	Make the best use of space by installing your icemaker under the counter
Stainless steel door	Professional styling with lasting durability
Professional towel bar handle	A curved handle in brushed stainless steel offers an easy grip

# BIM44GADA Specifications:

Overview	
Height of Cabinet	32.38" (82 cm)
Height to Hinge Cap	32.56" (83 cm)
Width	14.5" (37 cm)
Depth	23.5" (60 cm)
Depth with Handle	25.0" (64 cm)
Depth with door at 90°	36.75" (93 cm)
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	NSF
Amps	4.8
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs. (45 kg)
Shipping Weight	105.0 lbs. (48 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101021959
Icemaker	
Door Swing	LHD
Reversible	Yes
Drain Required	Yes
Daily Ice Production	50.0 lbs. (23 kg)
Ice Storage Capacity	25.0 lbs. (11 kg)
Ice Shape	Cube
Size of Cube	7/8" x 7/8" x 7/8"
Number of Ice Cube Sizes	1
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	3.88 oz.
High Side PSI	350.0
Low Side PSI	130.0
Interior Height	18.5" (47 cm)
Interior Width	12.0" (30 cm)
Interior Depth	16.0" (41 cm)

