

# BIM44GIF



33" x 14.5" x 23.5" (H x W x D)

Built-in NSF-listed automatic defrost clear icemaker with internal pump and integrated door frame to accept full overlay panels

### Highlights:

Commercial ENERGY STAR certification

Flexible design allows built-in or freestanding use in 15" wide spaces

Integrated door frame accepts full overlay panels for a true custom look

### Product Features:

ENERGY STAR certified commercial performance	Efficient performance for commercial use
Commercially approved	NSF listed for use in commercial establishments
Built-in capable	Make the best use of space by installing your appliance under the counter
Built-in pump	Internal pump allows more flexibility in placing the unit
Panel-ready door	Stainless steel door frame accepts full overlay panels to match adjacent cabinetry (panel size: 27 7/8" H x 14 5/8" W and at least 3/4" thick; maximum weight: 10 lbs.)
Automatic defrost	Reduced maintenance with auto defrost system
Insulated storage bin	Ice stays frozen longer inside this cold-protected bin
Clear ice cube production	Clear cubes offer the perfect cooling of your beverages; NOTE: ice is produced in sheets and can easily be broken into cubes using the provided scoop
Fully finished black cabinet	Allows the unit to be used freestanding



## BIM44GIF Specifications:

Overview	
Height of Cabinet	33.0" (84 cm)
Width	14.5" (37 cm)
Depth	23.5" (60 cm)
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	NSF
Amps	4.8
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs. (45 kg)
Shipping Weight	105.0 lbs. (48 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101027128
Icemaker	
Door Swing	LHD
Reversible	Factory Reversible
Drain Required	Yes
Daily Ice Production	50.0 lbs. (23 kg)
Ice Storage Capacity	25.0 lbs. (11 kg)
Ice Shape	Cube
Size of Cube	7/8" x 7/8" x 7/8"
Number of Ice Cube Sizes	1
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	3.88 oz.
High Side PSI	350.0
Low Side PSI	130.0
Interior Height	18.5" (47 cm)
Interior Width	12.0" (30 cm)
Interior Depth	16.0" (41 cm)
Level Legs	4

