



ALBV2466



31.63" x 23.5" x 23.38" (H x W x D)

Commercially approved 24" wide built-in ADA compliant beverage center designed for the display and refrigeration of beverages and food, with seamless stainless steel trimmed glass door and front lock

Highlights:

Sized to fit under lower ADA compliant counters

Flexible design allows for built-in or freestanding use in commercial or residential settings

Commercial grade design meets NSF-7 standards

Product Features:

ADA compliant	32" height allows for installation within ADA-compliant spaces
Commercially approved	ETL-S listed to NSF-7 commercial standards
Built-in capable	Front-breathing design allows the unit to be built-in under counters
Digital control panel	Makes for easy temperature reading/management with electronic controls inside
Seamless door frame	Single-piece door trim provides an elegant look
Double pane tempered glass door	Provides a full display of the interior, with two levels of glass for added protection
Factory installed lock	Keyed lock for secure interior, with two keys included
Adjustable shelving	Four shelves (3 wire, 1 glass) provide space and flexibility when organizing the interior's contents
Brake system shelving	Provides added safety when loading and unloading the unit's 4 shelves



ALBV2466 Specifications:

Overview	
Height of Cabinet	31.63" (80 cm)
Width	23.5" (60 cm)
Depth	23.38" (59 cm)
Depth with Handle	25.38" (64 cm)
Depth with door at 90°	45.75" (116 cm)
Capacity	4.2 cu.ft. (119 L)
Bottles	6 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	295.0kWh/year
Amps	1.25
Voltage/Frequency	115 V AC/60 Hz
Weight	112.0 lbs. (51 kg)
Shipping Weight	117.0 lbs. (53 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101063294
Refrigerator Features	
Sabbath Mode	Yes
Door Swing	RHD
Reversible	Yes
Height Adjustable	No
Shelf Type	Glass and Chrome
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	1.23oz.
High Side PSI	150.0
Low Side PSI	50.0
Level Legs Qty	2
Interior Light	Yes

Temperature Range	34 to 65°F
Sound Level	34.7 dB
Dimensions	
Interior Height	23.5" (60 cm)
Interior Width	19.0" (48 cm)
Interior Depth	17.0" (43 cm)
Compressor Step Height	5.5" (14 cm)
Compressor Step Width	19.0" (48 cm)
Compressor Step Depth	5.0" (13 cm)

