



# AL55



31.63" x 23.5" x 23.38" (H x W x D)

Built-in undercounter ADA compliant all-refrigerator with stainless steel door, black cabinet, door storage, lock, and digital controls

### Highlights:

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" wide spaces

Stainless steel door offers an elegant look

### Product Features:

ADA compliant	32" height allows for installation within ADA-compliant spaces
Commercially approved	ETL-S listed to NSF-7 commercial standards
Built-in capable	Front-breathing design allows the unit to be built-in under counters
Digital control panel	Makes for easy temperature reading/management with electronic controls inside
Factory installed lock	Keyed lock for secure interior, with two keys included
Stainless steel door	Durable construction with an stylish look
White interior	Classic interior allows for easy cleaning and viewing of products
Adjustable shelving	Three easy-glide shelves that extend 50% give space and flexibility when organizing the interior's contents
Brake shelving system	Provides added safety when loading and unloading the unit's 3 shelves



## AL55 Specifications:

Overview	
Height of Cabinet	31.63" (80 cm)
Width	23.5" (60 cm)
Depth	23.38" (59 cm)
Depth with Handle	25.38" (64 cm)
Depth with door at 90°	45.0" (114 cm)
Capacity	4.2 cu.ft. (119 L)
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	250.0kWh/year
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	95.0 lbs. (43 kg)
Shipping Weight	98.0 lbs. (44 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101063331
Refrigerator Features	
Sabbath Mode	Yes
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	2
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	1.23oz.
High Side PSI	150.0
Low Side PSI	50.0
Level Legs Qty	4
Interior Light	Yes
Temperature Range	36 to 46°F

Sound Level 33.7 dB

Dimensions	
Interior Height	23.5" (60 cm)
Interior Width	19.0" (48 cm)
Interior Depth	17.25" (44 cm)
Compressor Step Height	5.5" (14 cm)
Compressor Step Width	19.0" (48 cm)
Compressor Step Depth	5.0" (13 cm)

