



FF711ES



46" x 18.75" x 23" (H x W x D)

Two-door ENERGY STAR qualified refrigerator-freezer in 46" ADA compliant height; replaces FF71ES

Highlights:

Made in North America

ENERGY STAR qualified performance ensures annual savings

46" height for select ADA compliant applications

Product Features:

ENERGY STAR qualified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
CEE Tier II qualified	Efficient design meets CEE Tier II specifications, using 25% less energy than DOE standards require for this product category
Frost-free operation	No-frost convenience for reduced user maintenance
Thin-line design	Slim width under 19" for an easy fit in space-challenged kitchens
Clear crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer
Interior light	Automatically illuminates when you open the door
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Full freezer shelf	Organize your freezer contents with more options
Door storage	Store tall bottles and condiments right on the door for convenient access



FF711ES Specifications:

Overview	
Height of Cabinet	46.0" (117 cm)
Width	18.75" (48 cm)
Depth	23.0" (58 cm)
Depth with door at 90°	40.0" (102 cm)
Capacity	4.8 cu.ft. (136 L)
Defrost Type	Frost-Free
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	346.0kWh/year
Amps	0.9
Voltage/Frequency	115 V AC/60 Hz
Weight	102.0 lbs. (46 kg)
Shipping Weight	107.0 lbs. (49 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101079011
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	24.75" (63 cm)
Refrigerator - Interior Width	16.25" (41 cm)
Refrigerator - Interior Depth	15.75" (40 cm)
Refrigerator - Capacity	3.7 cu.ft
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	13.5" (34 cm)
Freezer - Interior Width	13.88" (35 cm)

Freezer - Interior Depth	12.5" (32 cm)
Freezer - Capacity	1.1 cu.ft
Freezer - Shelf Type	Wire
Freezer - Shelf Qty	1
Freezer - Full Door Shelves	2
Thermostat Type	Dial
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	1.2 oz.
Level Legs	2
Compressor Step Height	6.0" (15 cm)
Compressor Step Width	16.25" (41 cm)
Compressor Step Depth	6.5" (17 cm)

