










- Usable I.D.: Approx. 28.75" x 40.75" x 22.38"
- Capacity: 4000# Evenly Distributed Load.
- Stacking: 5 High Max./Static.
- Handling: 4" Under Clearance On All Sides.
- Finish: Unpainted Bare/Raw Steel.

*Note:Open Corners & Open Corrugated Ends, Unit Will Not Hold Liquids or Material Smaller Than a 5/8" Ball Bearing.




Global Industrial / T.I. © Copyright 2021

PROPRIETARY AND CONFIDENTIAL: THIS DRAWING AND INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF GLOBAL INDUSTRIAL'S VENDOR/MFR. T.I. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF GLOBAL INDUSTRIAL AND IT'S VENDOR/MANUFACTURER T.I. IS PROHIBITED.

| | | | | | |
|---|---|---|---|---|---|
| Job Description: | Dwn by: | Date Printed: | DECIMAL TOLERANCE AND UNITS ± .188 UNLESS NOTED ALL DIMENSION ARE IN INCHES | Angle Tolerance X° ± 1° | Global Item Number: 800106 |
| Global Contact: www.Globalindustrial.com (800) 645-2986 | Aprvd by: | Date Approved: | Last Saved By Date: | Prepared For: Global Industrial | Mfr. Part Number: 51018 / Global Part Number: 51018 |

GLOBAL INDUSTRIAL We can supply that.