








- Usable I.D.: Approx. 33.75" x 40.75" x 22.38"
- Capacity: 4000# Evenly Distributed Load.
- Stacking: 5 High Max./Static.
- Handling: 4" Under Clearance On All Sides.
- Finish: Unpainted Bare/Raw Steel.

*Note: Open Corners & Open Corrugated Ends, Unit Will Not Hold Liquids or Material Smaller Than a 5/8" Ball Bearing.







Global Industrial / T.I. © Copyright 2021

PROPRIETARY AND CONFIDENTIAL: THIS DRAWING AND INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF **GLOBAL INDUSTRIAL'S** VENDOR/MFR. T.I. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF **GLOBAL INDUSTRIAL** AND IT'S VENDOR/MANUFACTURER T.I. IS PROHIBITED.

Job Description:	Dwn by: JE	Date Printed:	DECIMAL TOLERANCE AND UNITS ± .188 UNLESS NOTED ALL DIMENSION ARE IN INCHES	Angle Tolerance X° ± 1°	
Global Contact: www.Globalindustrial.com (800) 645-2986	Aprvd by:	Date Approved:	Last Saved By Date:	Prepared For: Global Industrial	

GLOBAL INDUSTRIAL™ We can supply that.

Global Item Number: 800110M

Mfr. Part Number: 51007-DG42

Global Part Number: 51007DG