




WIRE SHELVING AND TRUCKS


ASSEMBLY INSTRUCTIONS



A FOR USE AS FREE-STANDING, STATIONARY SHELVING:


Before assembly, lay out storage area according to desired configuration. "T", "U", configurations may be used.

Insert tapered foot bushing into the bottom of each post. Seat securely by tapping with a rubber mallet. Screw the adjustable foot levelers into each bushing. After assembly, stand unit upright and adjust the foot levelers as required.



B FOR USE WITH STEM CASTERS:

Slip rubber bumpers over the bottom of each post. Push swivel stem casters into bottom of each post. Seat securely by tapping with a mallet. (Note: tapered foot bushing and levelers are not required when using stem casters.)



C FOR USE WITH DOLLY BASE:

Attach plate casters to dolly base with hardware provided. Insert the tapered foot bushing into the bottom of each post as shown in illustration "A". Seat securely by tapping with a mallet. Remove the assembly bolts, washers and nuts from each corner of the dolly base. Line up the shelving posts with the 4 corner holes on the dolly base. From the bottom of the base, insert bolt and washer up into bushing. Tighten securely.




STEP 1.

First perform "A", "B", or "C" according to the style you have selected. NOTE: Unit is erected from the bottom shelf up. Posts are grooved and numbered in 1" increments. (Number shown is approximate height of shelf from floor not including casters.)

STEP 2.

Select the height of lowest shelf.



STEP 3.

Hold one half of split sleeve against post with wider end down. Fit "ridge" inside the split sleeve into groove and snap split sleeve on. Then snap on the other matching half of the sleeve.

STEP 4.

Repeat Step 3 at the same height for each of the three remaining posts.



STEP 5.

Stand lowest shelf on its side. Insert posts from bottom into all four corners so the split sleeves fit inside each corner. Stand upright.

STEP 6.


At each corner, push shelf firmly down onto split sleeve. If necessary for a snug fit, tap corner lightly with a rubber mallet.

STEP 7.

Select height on the next lowest shelf. Repeat steps 3 and 4, from the top of standing unit, slide shelf onto post at all four corners so the split sleeve fits inside each collar. Repeat for remaining shelves.




FOR ADD-ON UNITS



STEP 8.

Following steps 2-7 on previous page, assemble add-on shelving using ONLY TWO POSTS.




STEP 9.

Two S-hooks included per shelf. Place hooks over shelf edge of free-standing unit and lower adjoining shelf edge of add-on unit onto hooks. Repeat for remaining shelves.


FOR BACK AND SIDE LEDGES:

Align ledge ends around post and snap onto shelf. Place bent wire inside the truss and the straight wire outside the truss.



TRAY SLIDE INSERT

Hook tray insert over front to back support wires of upper shelf. Lock tray insert into place on lower shelf.





UTILITY CART

ASSEMBLY INSTRUCTIONS



STEP 1.

NOTE: Unit is erected from top shelf down. U-handle posts are grooved 1" increments. Select height of top shelf.

STEP 2.

Place shelf on its side on floor. From top side of shelf, insert U-shaped handles into the four corners. Make sure handle tapers to the outside of shelf.



STEP 3.

Hold one half of split sleeves against post with wider end towards bottom of post. Fit "ridge" inside split sleeve into groove and snap split sleeve on. Then snap on the other matching half of the sleeve. Repeat for each of the other posts.



STEP 4.

Holding shelf upside down slide Next shelf down over posts.



STEP 5.

Select height of shelf and repeat step 4

STEP 6.

For three-shelf units repeat steps 4, 5 and 6 for remaining shelf.



STEP 8.

Slip rubber wheels bumpers over the bottom of each post, push swivel stem casters into bottom of each post. seat securely



STEP 9.

Stand cart upright and push each shelf firmly down onto split sleeve. If necessary for a snug fit, tap corner lightly with a rubber mallet.

CAUTION: Do not climb or stand on wire shelves. Do not drop heavy objects onto shelves. Ease heavy loads carefully onto unit. Distribute weight as evenly as possible

For best performance:

- Install bottom shelf as low as possible (for food service applications. (NSF requires the lowest shelf to be 6" {152mm} from the floor)
- Units over 50" (1270mm) high should be assembled with at least three shelves, and preferably four or more
- Adhere to shelf weight capacities
- Place shelving on solid and level floors
- Level the unit by adjusting the leveling bolts
- Do not drop heavy objects on shelves or subject units to shock such as forklifts or dollies
- Maintain casters with regular lubrication

! WARNING

TIPPING HAZARD

- Push mobile unit in long direction
- Do not stand or climb on shelving
- Place heavy objects on lowest shelf
- Inspect casters before use
- Replace worn casters immediately
- Distribute weight as evenly as possible

Failure to follow these instructions could result in personal injury or property damage