



GLOBALTM INDUSTRIAL

Forklift Blue Arrow Light with Flash

Technical Specifications:

- [LED] 9PCS Cree high power LEDs
- Beam: Arrow Beam with Flash
- Lux strength: 600LUX
- Voltage: 10~80V DC
- Color: Blue
- Life Time: >50000 Hours
- Working Temperature: -45 ~85°C
- Double insulated silicon rubberized wire, can bear very low&high temperature
- Reverse polarity protected
- Certificate: CE

NOTE: SAFETY MESSAGE TO INSTALLERS

People's lives depend on your safe installation of our products. It is important to read as below:

- To properly install this work light, you must have good understanding of automotive electrical procedures and systems, along with proficiency in the installation and use of safety warning equipment
- When drilling into a vehicle structure, be sure that both sides of the surface are clear of anything that could be damaged
- DO NOT install equipment or route wiring or cord in the deployment path of an air bag
- You should frequently inspect the light to ensure that it is operating properly
- This product contains high intensity LED devices. To prevent eyes damage, DO NOT stare into the light beam at close range
- Connect light wire to vehicle battery, black wire connect to negative pole, Red wire connect to positive pole
- Must fit a switch on the wire. If without switch, the light always keep to switch on