



# 8000BU-3900IA

PROFESSIONAL STEAM BOILER W/ HIGH PRESSURE IRONING STEAM WAND

The 8000BU provides continuous steam for an unlimited amount of time when it's hooked up to a direct water line or with the available 2 gallon water container. There's no more down time waiting for the boiler to re-pressurize. Paired with the 3900IA Ironing Steam Wand, it produces dry pressurized steam perfect for a wide variety of materials and applications.

Unlike a conventional steam iron, the 3900IA's unique ergonomic grip/handle can be used comfortably in any position, whether it's vertical like a steamer or horizontal like an iron. The aluminum soleplate provides more heat than our 3800IA brush and allows the user to press "hooks and cranny's" that would be challenging or impossible with a standard steam iron.

## SPECIFICATIONS

ELECTRICAL	120V	
WATER CAPACITY	Unlimited	
BOILER CAPACITY	1.25 GAL	4.5L
OPERATING PRESSURE	Up to 65 PSI	4.5 Bar
STEAM TEMPERATURE	221°F	105°C
HEATING ELEMENT	1200W	
STEAM WAND STANDARD	3900IA - 8.5' steam hose	
OPTIONAL IRON	2100IR - 7' steam hose	
OPTIONAL STEAM BRUSH	3800IA - 8.5' steam hose	
POWER CONSUMPTION	17 amps	
TANK CONSTRUCTION	Stainless steel	
LOW WATER INDICATOR	Standard	
STEAM CONNECTOR TYPE	Quick-release	
NET WEIGHT	34.5 lb (with wand)	15.6 kg (with wand)
SHIPPING WEIGHT	37.9 lb (with wand)	17.2 kg (with wand)
PRODUCT DIMENSIONS	10.75" x 11.25" x 20.5"	31 x 28.5 x 52 cm
SHIPPING DIMENSIONS	16" x 14.75" x 24.25"	40.5 x 3.57 x 61.5 cm
ELECTRICAL APPROVAL	ETL Special Inspection	
COUNTRY OF ORIGIN	Italy	
WARRANTY	Limited 1 year, 2 year tank	

## IT'S ALL ABOUT THE STEAM



PRESSURE GAUGE



BLOW DOWN VALVE



ADJUSTABLE FEET



MADE IN ITALY



QUICK RELEASE



BOILER TANK  
2 YEAR WARRANTY



THERMOSTAT  
RESET



5.5 BAR PRESSURE



DIRECT  
WATER FEED

