



8000CJ

AUTOMATIC JEWELRY STEAM CLEANER

The 8000CJ provides continuous steam for an unlimited amount of time when it's hooked up to a direct water line. There's no more down time waiting for the boiler to re-pressurize. The 8000CJ is the perfect choice for environments that require large volumes of uninterrupted steam.

The only ingredient required for the 8000CJ is water. Cleaning has never been safer, healthier or more environmentally friendly.

SPECIFICATIONS

ELECTRICAL	120V	
STEAM CAPACITY	Unlimited	
BOILER CAPACITY	1.25 GAL	4.5L
OPERATING PRESSURE	Up to 60 PSI	4 Bar
STEAM TEMPERATURE	221°F	105°C
HEATING ELEMENT	1200W	
POWER CONSUMPTION	17 amps	
TANK CONSTRUCTION	Stainless steel	
LOW WATER INDICATOR	Standard	
NET WEIGHT	26 lb	11.7 kg
SHIPPING WEIGHT	30 lb	13.6 kg
PRODUCT DIMENSIONS	11.5" x 11" x 23"	29 x 28 x 58.5 cm
SHIPPING DIMENSIONS	16 x 15" x 25"	40.5 x 38 x 63.5 cm
ELECTRICAL APPROVAL	cETLus	
WARRANTY	Limited 1 year, 2 year boiler tank	

CLEAN
WITH
STEAM



STAINLESS STEEL
ENCLOSURE



ADJUSTABLE FEET



PRESSURE GAUGE



MADE IN ITALY



CARRYING HANDLE



BOILER TANK
2 YEAR WARRANTY



THERMOSTAT
RESET



5.5 BAR PRESSURE



DIRECT
WATER FEED



8000CJ

AUTOMATIC JEWELRY STEAM CLEANER

