

Product information

86 03 180

Pliers Wrench

Pliers and a wrench in a single tool





- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings working directly on chrome!
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Fast adjustment by pushing a button directly on the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip, its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10: 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened



General		
Article No.	86 03 180	
EAN	4003773035466	
Pliers	chrome-plated	
Head	chrome-plated	
Handles	plastic coated	
Weight	230 g	
Dimensions	180 x 44 x 15 mm	
REACH compliant	no	
RohS compliant	no	

Technical details	
Jaw thickness (joint) (B2)	8.0 mm
Joint thickness (B3)	12.0 mm
Tips thickness (B1)	5.0 mm
Adjustment positions	15
Capacities for nuts	Ø 1 1/2 Inch
Capacities for nuts	40 mm



KNIPEX Quality – Made in Germany



Classification		
eCl@ss 5.1.4	21043826	
proficl@ss 6.0	AAA936c004	
UNSPSC 13.1	27112112	
Spare Parts		

Spare Parts

86 09 180 Range of spare parts adjustment for 86 XX 180,

technical change and errors excepted











