

Product information

87 00 100

KNIPEX Cobra® XS

Pipe Wrench and Water Pump Pliers

DIN ISO 8976



- Optimum accessibility, even in confined spaces: particularly compact design, very slim head
- One-handed fine adjustment by pushing for the simplest adjustment to different workpiece sizes
- Long-lasting secure grip ensured by high wear resistance
- Gripping capacity Ø 28 mm, width across flats up to 24 mm – at only 100 mm length
- Box joint: high quality and durability provided by dual guide
- Gripping surfaces with specially hardened teeth, hardness approx. 60 HRC
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Pinch guard prevents operators' fingers being pinched
- Fine adjustment with 11 adjustment positions

General

Article No.	87 00 100
EAN	4003773085836
Pliers	grey atramentized
Head	polished
Handles	embossed, rough surface
Weight	62 g
Dimensions	100 x 30 x 10 mm
Standard	DIN ISO 8976
REACH compliant	no
RohS compliant	no

Technical details

Adjustment positions	11
Capacities for nuts	Ø 1 Inch
Capacities for nuts	24 mm
Capacities for pipes (diameter)	Ø 28 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004

Spare Parts

87 09 100	Spare parts set for 87 0X 100,
-----------	--------------------------------

technical change and errors excepted



Self-locking and durable – all part of genuine KNIPEX water pump pliers



