

Product information

87 01 250

KNIPEX Cobra®

High-tech Water Pump Pliers

DIN ISO 8976





You Tube

General

- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx.
 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched

Assortment of spare parts for adjustment for 86/87 XX 250/300

Chrome vanadium electric steel, forged, multi stage oil-hardened

Article No.	87 01 250
EAN	4003773022022
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	335 g
Dimensions	250 x 44 x 14 mm
Standard	DIN ISO 8976
REACH compliant	no
RohS compliant	no
Technical details	
Adjustment positions	25
Capacities for nuts	Ø 2
Capacities for nuts	46 mm
Capacities for pipes (diameter)	Ø 50 mm
Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112
Spare Parts	


(without 87 2X XXX),

technical change and errors excepted

87 09 01

KNIPEX Quality – Made in Germany









Teeth set against the direction of rotation have a self-locking effect and prevent slipping on the workpiece.









KNIPEX Quality – Made in Germany







