

**DEWALT**

# WHERE SIZE MEETS POWER™

## DCD799 ATOMIC™ 20V MAX\* BRUSHLESS 1/2 IN. HAMMER DRILL

Unlock power in a compact size with the ATOMIC™ 20V MAX\* 1/2 in. Hammer Drill. Get up to 14% More Power\*\*\* with 585 UWO† for a variety of wood and masonry drilling applications in tight spaces with Our Shortest 20V MAX\* Hammer Drill\*\*. The on-tool LED worklight illuminates dimly lit spaces to optimize productivity on the job site.



**20V** MAX\*  
BRUSHLESS

**ATOMIC**  
COMPACT SERIES

\*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

\*\*DCD799 is Our Shortest 20V MAX\* Hammer Drill, tool head length only.

\*\*\*The DEWALT DCD799 with a DEWALT DCB230 battery (sold separately) provides up to 14% More Power vs. DEWALT DCD778 with a DEWALT DCB230 (sold separately).

†Based on using DCB205 battery

DCD799SS

# ATOMIC™ 20V MAX\* BRUSHLESS 1/2 IN. HAMMER DRILL

**1/2 IN. METAL CHUCK**

**15 CLUTCH SETTINGS**

**2-SPEED TRANSMISSION**  
0-450/0-1650 RPM

**HAMMER MODE**  
0-28,050 BPMs

**VARIABLE SPEED TRIGGER**  
For control in various applications

**FORWARD/REVERSE SWITCH**  
Quickly change direction of application

**ON-BOARD LED**  
Illuminate dark workspaces



OUR SHORTEST 20V MAX\* HAMMER DRILL\*\* at 6.5 in. (tool head length only) to access hard to reach spaces.



GET UP TO 14% MORE POWER\*\*\* and up to 1,650 RPMs for a variety of drilling applications.

\*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.  
\*\*DCD799 is Our Shortest 20V MAX\* Hammer Drill, tool head length only.  
\*\*\*The DEWALT DCD799 with a DEWALT DCB230 battery (sold separately) provides up to 14% More Power vs. DEWALT DCD778 with a DEWALT DCB230 (sold separately).  
†Based on using DCB205 battery

## SPECIFICATION

<b>TOOL HEIGHT</b>	7.97 in.
<b>TOOL WEIGHT</b>	2.6 lbs. (Tool only)
<b>TOOL LENGTH</b>	6.5 in. (Tool head length only)
<b>TOOL WIDTH</b>	2.49 in.
<b>BPMS</b>	0-28,050
<b>CHUNCK SIZE</b>	1/2 in. metal
<b>CLUTCH SETTINGS</b>	15
<b>SPEED SETTINGS</b>	2
<b>NO LOAD SPEED</b>	0-450/0-1,650 RPM
<b>MOTOR TYPE</b>	Brushless
<b>MAX POWER</b>	585 UW0†

## KIT OPTIONS

### DCD799B

- (1) DCD799 ATOMIC™ 20V MAX\* 1/2 in. Hammer Drill
- (1) Belt hook



### DCD799P1

- (1) DCD799 ATOMIC™ 20V MAX\* 1/2 in. Hammer Drill
- (1) DCB205 20V MAX\* 5Ah Battery
- (1) Belt Hook
- (1) Charger
- (1) Kit Bag



## WARRANTY

**3**  
YEAR

LIMITED WARRANTY

**1**  
YEAR

FREE SERVICE

**90**  
DAY

MONEY BACK GUARANTEE

## RELATED PRODUCTS

### DCD794B

ATOMIC™ 20V MAX\*  
Brushless 1/2 in. Drill /Driver  
(Tool Only)

