



DCK2101QQ1WW1 20V MAX* XR® HAMMER DRILL/IMPACT 2-TOOL COMBO KIT WITH XR POWERPACK™ BATTERIES

- OUR MOST POWERFUL 20V MAX* HAMMER DRILL** (DCD1007)
- PRIORITIZE PRODUCTIVITY: Up to 275 holes per charge† (DCD1007)
- BRUSHLESS MOTOR: Delivers 1,825 in.-lbs. of torque and 3,400 RPM (DCF845)
- PART OF OUR BEST PERFORMING LINE of 20V MAX* power tools and batteries‡



*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

**Based on rated maximum watts out for DEWALT 20V MAX* hammer drills currently on the market.

†Using DCB2108 battery and 7/8 in. diameter auger in 1-1/2 in. thick fir.

‡Regarding battery, based on longer life (charge cycles) and more power, not in application vs. DEWALT 20V MAX* batteries with comparable amp hours.

¹1530 MWO based on using DCB2108 battery included.

²1211 MWO based on using DCB2104 battery included.



MAX POWER
1530 MWO¹
1211 MWO²
(DCD1007)

**NO-LOAD
SPEED**
UP TO 3,400 RPM
(DCF845)

Includes: (1) DCD1007 3-Speed Hammer Drill, Side Handle, (1) DCF845 XR® Impact Driver, (1) DCB2104 XR POWERPACK™ 4Ah Batteries, (1) DCB2108 DEWALT POWERPACK™ 8Ah Battery, (1) Charger, (2) Belt Hooks, (1) Kit Bag.

© 2025 DEWALT

ICDCK2101QQ1WW1FT