

1,500 PSI - 1.6 GPM ELECTRIC PRESSURE WASHER WITH POWEREASE MOTOR AND AXIAL PUMP

MODEL: B1515EN

WORKSHOP

SERIES

FEATURES

- **Electric motor** is rated at 1.5 HP, quiet running, and can be safely used indoors.
- **Equipped with a GFCI plug** that greatly reduces the risk of electric shock.
- **Triplex pump** with forged brass manifold, ceramic coated pistons, built-in soap injector and thermal valve.
- **Built-In unloader** effectively regulates water flow in a compact design.
- **Accessories** include high-pressure hose, spray gun wand assembly with a variable nozzle so that it can be used right out of the box.
- **Powder coated steel frame** with storage for accessories, and 10" flat free tires easily handles going over rough terrain.



Scan the QR code with your mobile device and discover more about this BE pressure washer.

PLUG TYPE



NEMA 5-15P



CSA CERTIFIED

MOTOR

MODEL:	POWEREASE
HORSE POWER:	1.5
AMPS:	13
VOLTS:	120
CORD LENGTH	25'

PUMP SPECS

MODEL:	POWEREASE
TYPE:	TRIPLEX
OIL TYPE:	30W NON-DETERGENT
PART NUMBER:	85.165.014

UNLOADER

TYPE:	BUILT-IN
PART NUMBER:	85.165.010

FRAME

MATERIAL:	POWDER COATED STEEL
WHEELS:	10" FLAT FREE

ACCESSORIES

HOSE TYPE:	25" X 1/4" RUBBER
PART NUMBER:	85.225.128
NOZZLE:	0°, 15°, 40° AND SOAPER
PART NUMBER:	85.210.025BEP
GUN WAND:	36"
PART NUMBER:	85.205.050
FITTINGS:	M22 THREADED

BOXED SIZE

LxWxH:	23" x 22" x 20"
WEIGHT:	80 LBS

UNIT SIZE



UNIT WEIGHT: 75 LBS

WARRANTY

MOTOR:	2 YEARS
PUMP:	2 YEARS
UPC:	777897166231

03-2021