Product Name:	PH-ABT-HC-RFC7S-CAD
Description:	
	Max air temp in empty freezer: 5°F (-15°C) Max air temp in loaded freezer: 3°F (-16°C) Max sample temp in empty freezer: 0°F (-18°C) Max sample temp in loaded freezer: -4°F (-20°C) Refrigerator/Freezer freestanding thermometer with 3 year certificate of calibration, with min/max memory, °F/°C switchable Audible and visual high and low temperature alarms, refrigerator and freezer
	Remote alarm contacts, refrigerator and freezer 5 adjustable shelves total with guard rail on back to prevent product from being pushed against back wall 3 adjustable shelves, Refrigerator; 2 adjustable shelves, Freezer Bottom footed shelf to allow air circulation, Refrigerator and Freezer Vaccine storage power cord warning label Forced draft circulation Refrigerator Keyed door locks Magnetic door gasket for positive seal Integrated door handles Leveling legs Stacking kit
	Two probe access ports (3/8"); one, refrigerator/one, freezer White powder coated exterior HFC-free refrigerant (R600a), foam insulation and packaging Pharmacy refrigerator/freezer toolkit and temperature logs Two year parts and labor warranty, plus an additional three year compressor parts warranty Pyxis®, Omnicell ®and AcuDose RX® compatible Exterior dimensions: 23 ¾"W x 24" D x 53 1/8"H Controlled auto defrost freezer / cycle defrost refrigerator

115V, 60 Hz, 1.3 Amps refrigerator, 1 Amp freezer, 1/6
HP refrigerator, 1/8 HP freezer
UL/C-UL listed
Shipping weight: 215 lbs.
*Please note this unit requires 2 outlets.
'