



TECHNICAL SPECIFICATIONS

Power Breezer

VOLTS	INDUSTRIAL PART NUMBER
110V	PB10-A-06-B
220V	PB20-A-1B

Cooling Capacity	31,500 Btu		
Wind Range	Up to 65 feet (20 meters)		
Air Speed (Miles Per Hour)	10 Feet	20 Feet	40 Feet
	16	10	5
Variable Atomized Cooling Control	Yes		
Oscillation	Yes		
Electrical Consumption	Avg. 13.64 Amps, 1,300 Watts		
Water Consumption	Up to 4 Gallons/Hour (15.1 L/Hour)		
Integrated Water Container	Yes - 85 gallons (322 liters) Water hose connection not required.		
Height	46.92" (119.2cm) stored, 73.52" (186.7cm) mounted		
Width	29.64" (75.3cm)		
Depth	45.38" (115.3cm) stored, 53.96" (137.0cm) mounted		
Weight (without water)	240 lbs. (108.86kg)		
Power Source	110V or 220V (Type G Plug)		
Motor	1 hp E		
Technology	Unique atomization technology		
Wheels/Casters	10" (25.4cm) locking wheels and 7" (17.78 cm) casters		
Hard case for shipping and transport	Yes - Integrated into design		
Certifications	OSHA Compliant, ETL Certified, MIL-STD 810G Certified CE Compliant, NOM Pending		
Limited Warranty	2 Years		