



AC Hydraulic^{AS}
NO COMPROMISE

By



50-2 AIR HYDRAULIC JACK

2-Stage Air Hydraulic Jack

- 2-stage air hydraulic jack for heavy buses and trucks
- Minimum height of 8.66 in (220 mm)
- Designed for heavy-duty, intensive commercial use
- Hard chromium plated piston rod for long life
- Built-in safety overload valve
- Hand-operated dead-man's control for optimum safety while lifting and lowering
- 50-2TH model with telescopic handle increasing the reach under the vehicle to 85.43 in (2170 mm) ensuring safe and easy operation
- With 2 extensions (50/100 mm)



Technical data	50-2	
Capacity	11000 / 55000 lb	50 / 25 t
Min. height	8.66 in	220 mm
Max. height	13.39 / 17.72 in	340 / 450 mm
Frame length	31.82 in	810 mm
Handle length	53.35 in	1355 mm
Width	7.87 in	200 mm
Width (with wheels)	12.40 in	315 mm
Air supply	9 - 12 bar	9 - 12 bar
Air consumption	350 l/min	350 l/min
Weight	176 lb	80 kg