

# Ten Reasons why you'll LYVE Bonita USA



- 1. Prices as Low as \$1,145 (base only). We strive to produce the highest quality and affordable products for our customers.
- 2. Height Range: 27" 47". Quiet lift with virtually no sound and standard up/down button control which can be soft programmed with container stops.
- 3. Lifting Capacity: 250 pounds utilizing German gears and Austrian controls with a superior glide system.
- 4. Height Adjustment: 1.5 inches per second. Plus our smart load protection technology senses overloading and will shut down the system to avoid damage to the desk.
- **5. Stability** We utilize a lower cross support to create one of the most stable height adjustable tables not normally found. NO WOBBLE.

- **6.** Contemporary Style a clean look with an attractive silver or black base finish available with ten LPL laminate worksurface options.
- 7. Sustainable low power consumption which means less emissions and power used.
- **8. 4EVERedge Edge Banding** State-of-the-art hot air technology features virtually invisible edge banding. Available in Hardrock Maple, Cherry and White.
- 9. Built to Last Built in the USA. RightAngle Products utilize the highest standards of design, engineering and production practices.
- 10. Warranty: ten years support brackets, columns and feet; five years - gears and/or motors, electrical components.







#### **Bonita ET Features**

- Height Range: 27" 47" H.
- Total Lifting Capacity Base Only: 250 pounds 2-leg, 350 pounds 3-leg.
- Control Box Configurable stop conditions (overtemperature, overcurrent, timeout, limit switches).
- Height Adjustment: 1.5 inches per second.
- Available with worksurface or base only.
- Standard depth 24" and 30".
- Mounting clearance (depth) for under desk accessories (note: any length track system can be mounted on an angle): 24" workstation is 14" 30" workstation is 17".
- Anti-wobble cross support.
- Recommend only the trackless keyboard arm system (TLF).

See Spec Book for complete specifications: raproducts.com/price





### **Finishes**

#### **Laminate Surface Colors**

Featuring ten laminate colors with coordinating edge band options. High-pressure laminate and custom colors available.



Hardrock Maple (HM)◆



Stromboli (ST)



Mahogany (MY)



Cherry (CH)◆



**Base Colors** 



Silver (S)



Black (BK)◆



Driftwood (DW)\*\* Concrete Groovz (CG)\*\*



Merapi (ME)\*\*



Gray Matrix (GM)◆\*\*\*



**Finish Options** (Only Available on Standard 24" and 30" Configurations)



Black Base (B) Cherry Top (CH)



Silver Base (S) Cherry Top (CH)



Black Base (B) Hardrock Maple Top (HM)



Silver Base (S) Hardrock Maple Top (HM)

## Galaxy White (GW)◆ ♦ Includes 4EVERedge™ edge banding for straight line worksurfaces

- \*\*Driftwood, Concrete Groovz, and, Merapi have Graphite edge banding
- \*\*\*Gray Matrix has Black edge banding

# You may also like...





















