

OPF-P PRECISION COUNTING BALANCES



SPECIFICATIONS

READABILITY: 0.1g, 0.2g, 0.5g, 1g

REPEATABILITY: $\pm 0.1g$, 0.2g, 0.5g, 1g

LINEARITY: $\pm 0.2g$, 0.4g, 1g, 2g

INTERNAL RESOLUTION:

600,000 graduations

COUNT CAPACITY:

999,999 pieces

UNIT WEIGHT MEMORY: 21 items

RESPONSE TIME: 2 seconds

POWER (AC ADAPTER):

110V-240VAC, 50HZ/60HZ

OPERATIONAL TEMPERATURE:

50°F - 86°F

CONSTRUCTION:

Cast aluminum, static resistant ABS

KEYPAD: 32 keys, Splash-proof

WARRANTY:

1 year limited warranty

FEATURES

- Vibrating technology provides the highest level of counting accuracy
- 30,000 displayed resolutions
- 3 displays (weight, unit weight, count)
- Up to 21 PLU (Product Look Up) for storing sample weights so they can be easily retrieved
- Truly portable with both AC adapter and rechargeable battery that lasts up to 100 hrs
- High visibility back lit LCD display
- Durable ABS housing and large anti-static stainless steel pan
- Warning for insufficient unit piece weight and sample size
- Multiple weighing units: g, kg, lb, oz, pcs
- Overload alarm
- Leveling feet with bubble level
- Weight and piece count show simultaneously
- Portable rugged design

PART#	CAPACITY	DIMENSIONS	PAN SIZE	SHIP WT.
OPF-P3	3 kg x 0.1 g	13" L x 13.5" W x 4" H	13.3" x 9"	10 lbs
OPF-P6	7.5 kg x 0.2 g	13" L x 13.5" W x 4" H	13.3" x 9"	10 lbs
OPF-P15	15 kg x 0.5 g	13" L x 13.5" W x 4" H	13.3" x 9"	10 lbs
OPF-P30	30 kg x 1 g	13" L x 13.5" W x 4" H	13.3" x 9"	10 lbs

