

OP-915SS STAINLESS STEEL BENCH SCALES



HIGH PRECISION



STANDARD



FEATURES

- Stainless steel base, stainless steel platform
- Large 0.9" backlit LCD indicator with a rechargeable battery and watersealed AC Adapter
- Stainless steel load cell with hardwired cable to indicator for maximum water protection
- Detachable column and tilt stand for table, wall or under counter mounting
- Overload stops on scale base
- Measurement units: lb, kg (g, lb:oz, oz - Not Legal for Trade)
- Lower/upper limit alarm
- Counting feature (Not Legal for Trade)
- Accumulation feature
- Check-weighing feature for quick portioning
- Level bubble

SPECIFICATIONS

- **POWER:** 6V 4Ah rechargeable lead acid battery with 110V power supply
- **FREQUENCY:** 50 or 60 Hz
- **SERIAL COMMUNICATIONS:** Full duplex RS-232, 9600, 4800, 2400, 1200 bps; 8 data bits, 1 stop bits, no parity, no handshaking
- **OPERATING TEMPERATURE:** 5°F to 104°F (-4°C to 40°C)
- **IP RATING:** IP67
- **WARRANTY:** 1 year limited warranty
- **APPROVALS:** NTEP CC 11-016, Class III 5,000 d; Measurement Canada AM-5817, Class III 5,000 d

PART#	DESCRIPTION	CAPACITY	PLATFORM SIZE	WEIGHT
HIGH PRECISION¹ (INC. INDICATOR AND COLUMN)				
OP-915SS-HP-6	All Stainless Steel High Precision	6lb x 0.0002lb / 3kg x 0.1g	10" x 10" x 4" H	21 lbs
OP-915SS-HP-15		15lb x 0.0005lb / 7.5kg x 0.2g	10" x 10" x 4" H	21 lbs
OP-915SS-HP-30		30lb x 0.001lb / 15kg x 0.5g	10" x 10" x 4" H	21 lbs
OP-915SS-HP-60		60lb x 0.002lb / 30kg x 1 g	10" x 10" x 4" H	21 lbs
STANDARD (INC. INDICATOR AND COLUMN)				
OP-915SS-1212-100	All Stainless Steel	100 lb x 0.02 lb	12" x 12" x 4" H	29 lbs
OP-915SS-1214-150	All Stainless Steel	150 lb x 0.02 lb	12" x 14" x 4" H	31 lbs
OP-915SS-1616-300	All Stainless Steel	300 lb x 0.05 lb	16" x 16" x 4.25" H	40 lbs
OP-915SS-1620-400	All Stainless Steel	400 lb x 0.05 lb	16" x 20" x 4.25" H	47 lbs
OP-915SS-1818-400	All Stainless Steel	400 lb x 0.05 lb	18" x 18" x 4.25" H	47 lbs
OP-915SS-2020-500	All Stainless Steel	500 lb x 0.1 lb	20" x 20" x 4.25" H	66 lbs
OP-915SS-1824-500	All Stainless Steel	500 lb x 0.1 lb	18" x 24" x 5.5" H	66 lbs
OP-915SS-2424-500	All Stainless Steel	500 lb x 0.1 lb	24" x 24" x 5.5" H	86 lbs
OP-915SS-2424-1K	All Stainless Steel	1,000 lb x 0.2 lb	24" x 24" x 5.5" H	87 lbs

