

ANSI SPECS

Finished Minimum Dimensions of Limited-Use and Disposal Protective Coveralls

	X-SMALL	SMALL	MEDIUM	LARGE	X-LARGE	2X-LARGE	3X-LARGE	4X-LARGE	5X-LARGE
CHEST (1)	20.5"	22.0"	23.5"	25.0"	26.5"	28.0"	29.5"	31.0"	32.5"
INSEAM (2)	26.5"	27.5"	28.0"	29.0"	29.5"	30.5"	31.5"	32.0"	32.5"
SLEEVE OUTSEAM (3)	29.0"	31.0"	32.5"	33.5"	35.0"	36.5"	37.0"	38.0"	39.0"
BODY LENGTH (4)	31.0"	33.0"	35.0"	37.0"	38.5"	40.5"	42.5"	43.5"	44.5"
SLEEVE OPENING (5)	5.5"	5.5"	6.0"	6.0"	6.0"	6.0"	6.5"	6.5"	6.5"
LEG OPENING (6)	9.5"	9.5"	10.0"	10.0"	10.0"	10.0"	10.5"	10.5"	10.5"
FRONT OPENING (7)	21.5"	21.5"	25.5"	25.5"	25.5"	27.5"	27.5"	27.5"	28.0"

\*\*\*allowable tolerance and variance +/- 0.5"\*\*\*