

HB - 3 5



MAXIMUFF™ HIGH PERFORMANCE DIELECTRIC EAR MUFF WITH INDESTRUCTIBLE HEADBAND AND SMART FOLD-OUT DESIGN

Ref. WELHB35\_



#### Product specifications

The MaxiMuff™ is a high performance ear muff, providing hearing protection in the most challenging environments without sacrificing comfort.  
Rugged, fully dielectric construction protects workers from electrical shocks and shorts.

Headband: Acetyl  
Ear Cup: ABS  
Foam Absorber: Polyurethane  
Ear Cushion: PVC

**COLOR**  
Yellow, Black

**SIZE**  
No size

## Product Use - Risks



Noise



Agriculture / Green areas  
craftman



Construction / Civil engineering



Second work /



Heavy industry



Light industry



Services / Logistics



Hygiene environment



Oil / Gas



Mining



Wind/Energy

## Product's highlights & user's benefits

Comfortable, yet tough unbreakable multi-position headband.

Exclusive ELVEX® "smart fold-out" design, muffs fold-out and rest comfortably around neck when not in use.

Self-aligning suspension on headband for quick fitting and adjustment.

Soft, pliable SuperSeal™ ear cushions are long lasting and resist body oil and sweat.

Multi-position use with or without optional support strap for compatibility when worn with other hats.

## Certifications and Standards

### USA STANDARDS



ANSI S12.6 Hearing Protection Attenuation Standard - ANSI S12.6



ANSI S3.19

28 NRR: NRR – (Noise Reduction Rating - Noise Reduction Rating)



89/686/EEC PPE DIRECTIVE

EN352-1 Earing protection : Ear-muff



30 SNR: Standard noise reduction

H 32: High frequency attenuation

M 28: Medium frequency attenuation

L 18: Low frequency attenuation

## References

References	Bar code	COLOR	SIZE		
WELHB35	7292948235070	Black	No size	24	-
WELHB35Y	3295249224516	Yellow	No size	2	-