

VERSAMATE-300

If you are looking for a simple and versatile solution for applying labels to flat items such as bags, pouches and envelopes, look no further! The VERSAMATE-300 enables you to label all kinds of flat objects by simply inserting them and watching the machine do the work. The sensors are activated automatically, and the label is applied at over 4.5" per second. Most items are labeled in less than 3 seconds! The Heavy-Duty construction of the VERSAMATE-300 will withstand the most high volume production environments.



VERSAMATE-300

Technical Specifications	VERSAMATE-300
Labels Applied per Object	1
Max Label Liner Width (in)	11.5 (292-mm)
Min Label Liner Width (in)	1.5 (38-mm)
Min Label Length (in)	1 (25-mm)
Max Object Thickness (in)	0.20 (5-mm)
Max Roll Diameter (in)	9 (230-mm)
Core Diameter (in)	0.5 - 6 (13 - 152-mm)
Label Types	Opaque & Transparent
Max Speed (items per hour)	1,200
Dimensions-HWD (in)	8 x 21 x 19 (203 x 533 x 483-mm)
Weight (lbs)	29 (13.2-kg)
Input Power Specifications ¹	120V or 220V
Warranty	3 year limited warranty

1. Specify desired voltage at time of order.