

POWERTEC 727 CS

High Security Paper | Optical Media Shredder

Special Features



Security Level



Security Level



NSA Approved



Chain Driven Motor



EvenFlow Lubricator



Jam Protection



Precision Engineered

The PowerTEC 727 CS High Security Combination Shredder is NSA approved for the top-secret destruction of paper and optical media. It features a powerful chain driven motor, an automatic EvenFlow Lubricator, and simple push button operation. This P-7/O-5 shredder is NSA rated for high volume shredding and holds up to 53 gallons of waste. It's precision engineered and supports the high security shredding needs of military and government agencies.



LED keypad with easy-to-use controls for simple operation.

Features/Benefits

- NSA/CSS 02-01 / NSA/CSS 04-02 Approved for Top-Secret data destruction
- Powerful paper and optical media combination shredder
- Chain driven continuous duty motor for slip-free power
- Automatic EvenFlow Lubricator provides continuous oil across the cutting cylinders
- Automatic jam protection eliminates frustration
- LED keypad with easy-to-use controls for simple operation
- Rubber shock mounts suspend the cutting head and reduce vibration
- Self-cleaning mode ensures optimal performance



Chain-driven continuous duty motor for maximum power.



727cs Specifications

Security Level	NSA Approved	Capacity #20 / #16	Shred Size	Waste Volume paper media	Feed Width paper media	Speed feet/min
P-7 O-5	Yes	11 / 13	1mm x 5mm	33 gal. 20 gal.	9" 5"	24
Motor	Decibel Level	Warranty Machine Cylinders	Dimensions length x width x height	Weight	Power Supply	
3.5 Hp	55	2 Years 1 Year	21.75" x 28" x 43"	330 lbs	115v	