HSM SECURIO AF100 Autofeed document shredder





- High quality materials and "Made in Germany" quality for security and durability; complete with a 3 year warranty
- Cutting rollers made of hardened solid steel
- Reliable and time-saving paper shredding of stacks of paper
- Nanogrip technology for reliable sheet intake
- Energy Management Control System: zero power consumption in stand-by mode
- Paper feed with overload protection reduces paper jams
- Quiet operation minimizes noise development in the workplace
- Practical automatic start/stop
- Level indicator through inspection window in the waste container
- Effortless emptying of the waste container via the removable housing top



HSM Part #	HSM2063	
Cutting type	cross cut	
Cutting size	5/32" × 1"	
Security level DIN 32757-1	3	
Security level ISO/IEC 21964 (DIN 66399)	P-4 T-4 E-3 F-1	
Cutting capacity per run in sheets (Autofeed/Manual)	100 / 5-6	
Cutting Speed	8.9 ft / min	
Full Hopper Speed (min)	10.67	
Throat opening	8.9"	
Motor power (horsepower)	0.4 hp	
Voltage	120V / 60Hz	
Dimensions (H x W x D)	24.4" x 14.7" x 10.2"	
Weight	15.4 lbs	
Shred-bin volume	6.6 gal	
Cutting capabilites		

All technical specifications are approximate values. Technical and design modifications reserved.

* Autofeed paper tray is for paper only

HSM of America, LLC 419 Boot Road Downingtown, PA 19335 www.hsmofamerica.com Customer Service: 800.613.2110



Copyright © 2018 by HSM° of America