



SPECIFICATIONS

Product Description: **HI-VIZ HEAVY DUTY SCBA WALL CASE**
 Part Number: **4125 and 4325**
 Style: **SINGLE AND DUAL ROTO MOLDED CASE**

GENERAL DESCRIPTION:

The 4125 and 4325 are cases designed for the storage of wall mounted SCBA's. They provide protection from dust moisture and damaging plant environments. The LLDPE material is Roto-Molded making it very light weight but extremely rugged. The 4125 Single has two viewing windows and the 4325 has four viewing windows to allow easy visibility of the SCBA gauges. The Universal Cylinder Bracket and Cylinder Strap support the entire weight of the SCBA and keep it secure inside the case. The molded in door handle helps to give this case a low profile when mounted to the wall.



CONSTRUCTION:

- Rugged Linear Low Density Polyethylene (LLDPE)
- UV Stabilizer additives
- Color is HI-VIZ Yellow
- Molded in tabs allow for easy opening and closing of door
- Recessed door handle allows for low profile design
- Single or Dual Case design
- Simple fast installation
- Complete with universal cylinder bracket and cylinder strap
- Recyclable



BRACKET:

Size: Universal
 Material: Powder coated mild steel
 Straps: Nylon straps for cylinder security

DIMENSIONS:

Part Number	Width In (cm)	Depth In (cm)	Height In (cm)	Interior			Weight	
				Width In (cm)	Depth In (cm)	Height In (cm)	Shipping Lb (Kg)	Product Lb (Kg)
4125	17" (43.1)	14" (35.5)	32" (81.2)	15 3/4" (40.0)	12 3/4" (32.3)	28" (71.1)	21 Lbs (9.5)	18 Lbs (8.1)
4325	34" (86.3)	14" (35.5)	32" (81.2)	*31 1/2" (80.0)	12 3/4" (32.2)	28" (71.1)	42 Lbs (19.05)	38 Lbs (17.2)

*Dual wall divided into two equal storage areas (2 x15 3/4" (40.0 cm))