



## SPECIFICATIONS

Product Description: **PANEL, AIR FILTRATION**  
 Part Number: **9874-MR and 9876-MR**  
 Style: **PORTABLE, 4 and 6 WORKER SYSTEMS**

### GENERAL DESCRIPTION:

Allegro air filtration panels filter impurities and hydrocarbons from an air compressor to convert to breathable air. A CO monitor is integrated to meet OSHA requirements for continuous monitoring of carbon monoxide levels. The panels provide 60 CFM (101.94 m<sup>3</sup>/hr) or 100 CFM (169.9 m<sup>3</sup>/hr) of air within a 5-125 PSI (.34-8.62 bar) range. The unique design of these panels allows each regulator to be individually adjusted at different pressure settings, allowing as well, separate outlets to be used for air tools (fittings used for breathing air must not be compatible with other plant/tool air fittings, contact Technical Support for details).

### CONSTRUCTION:

- Housed in a portable, rugged Pelican case with carrying handle and latches for protection and security
- Acrylic window to monitor pressure gauges
- Black powder coated, 16 gauge steel stand for support
- All brass plumbing with Quick-Disconnect Hansen couplers

### CO MONITOR:

Power source: 115 VAC to 9 VDC adapter for continuous power  
 9V DC Alkaline battery (back-up for AC adapter)  
 Alarm Setting: 10 PPM (Canada: 5PPM)  
 Ext. Connections: For optional Remote Strobe Alarm  
 Audible: 90 decibel Piezo Alarm  
 Visual: External power LED light signal  
 Sensor: Electrochemical, replaceable  
 Display: Liquid crystal  
 Keys: Mode & Set  
 Modes: Normal operation, peak, battery charge and calibration mode  
 Calibration: Self adjusting calibration to 20 PPM CO

### FILTRATION SYSTEM:

First Stage: 5 micron particulate filter element and automatic mechanical drain  
 Second Stage: 0.010 micron coalescing filter element and manual drain  
 Third Stage: 0.003 ppm activated carbon filter element and manual drain  
 Regulator: Individual, high pressure, adjusting pressure knob, ABS cover, 0 -160 psi (0-11.03 bar) pressure gauge and an external relief valve set at 125 psi (8.62 bar)  
 Flow Meter: Adjustable metering valve, range from 0.0 -1.0 LPM

### DIMENSIONS:

Model	Length In. (cm)	Width In. (cm)	Height In. (cm)	Weight Lbs. (Kg)
9874-MR	21" (53.3 cm)	6 ¾" (17.1 cm)	14½" (36.83 cm)	21 lbs (9.5 kg)
9876-MR	23" (58.4 cm)	7½" (19.05 cm)	16½" (41.9 cm)	27 lbs (12.2 kg)



9874-MR



9876-MR