



SPECIFICATIONS

Product Description: PANEL, AIR FILTRATION 9875-40. 9875-40W/O

Style: WALL MOUNTED, 5 WORKER SYSTEM

GENERAL DESCRIPTION:

Allegro air filtration panels filter impurities and hydrocarbons from an air compressor to convert to breathable air. To meet OSHA requirements an optional CO monitor is available for continuous monitoring of carbon monoxide levels. Panel provides up to 60 CFM (101.94 m³/hr) of air within a 5-125 PSI (0.34-8.62 bar) range.



CONSTRUCTION:

- A 12 gauge, black powder coated steel bracket for mounting
- All brass plumbing with quick-disconnect Hansen couplers

CO MONITOR:

Power Source: 115V AC to 9V DC power adapter for continuous power supply

9V DC Alkaline battery (primary or as back up for AC adapter)

Alarm Setting: 10 PPM (Canada: 5 PPM)
Ext. Connections: Optional strobe light alarm
Audible: 90 decibel Piezo alarm

Visual: External power LED light signal Sensor: Electrochemical, replaceable

Display: Liquid crystal Keys: Mode & Set

Modes: Normal operation, peak, battery charge and calibration mode

Calibration: Self adjusting calibration to 20 PPM CO

FILTRATION SYSTEM:

First Stage: 5 micron particulate filter element and automatic mechanical drain

Second Stage: 0.010 micron coalescing filter element and manual drain
Third Stage: 0.003 ppm activated carbon filter element and manual drain

Regulator: High pressure, adjusting pressure knob, ABS cover, 0-160 psi (0-11.03 bar)

pressure gauge and an external relief valve set at 125 psi (8.62 bar)

DIMENSIONS:

Length In. (cm)	Width In. (cm)	Height In. (cm)	Weight Lbs. (Kg)
22" (55.8 cm)	7" (17.7 cm)	7¾" (19.6 cm)	15 lbs (6.8 kg)

1360 Shiloh Church Road Piedmont, SC 29673 864-846-8740 800-622-3530 FAX: 800-362-7231 <u>www.allegrosafety.com</u>

Rev G 2-7-18