

SPECIFICATIONS

Product Description: **SOURCE PRE-FILTER**
Style: **REMOTE**

GENERAL DESCRIPTION:

Where air quality is especially low, this free-standing or wall-mounted particulate assembly helps extend the life of the filter panel's disposable filters by removing liquids and contaminants down to 5 microns. It is equipped with an adjustable high pressure regulator and gauge to meet the NIOSH requirement for point-of-attachment.

CONSTRUCTION:

Stand: Powder coated steel
Relief valve: Brass, spring loaded (External)
Max Temperature: 150°F (65.5°C)
Fittings: ½" Quick-Connect Hansen

REGULATOR & MANIFOLD:

Maximum pressure: 250 psi (17,2 bar)
Flow Capacity: 165 CFM
Manifold: Zinc
Adjusting knob: Acetal
Body Cap: ABS
Valve: Balanced Valve Design, Brass/Nitrile
Diaphragm: Spring loaded, Nitrile/Zinc
Pressure gauge: Analog, 0-300 psi, 1½" diameter



FILTRATION BOWL:

Bowl: Zinc, with a Polycarbonate sight gauge
Element retainer: Acetal
Useful Retention: 2.87 oz (84.9cm²)
Seal: Nitrile

FILTER ELEMENT:

Standard Filtration: 5 Micron
Element Type: Coalescing
Material: Sintered Polyethylene
Drain: Automatic mechanical with float

DIMENSIONS:

Depth	Width	Height	Weight
9"	6¼"	13 15/16"	3.5 lbs