

Facial Flat Angel Soft ps 100/30

Enhance your image by enhancing your customers' experience with our premium facial tissue!



Description:

Now you can roll out the white carpet for your customers by offering the luxury of at-home softness and appearance and the assurance of a nationally known quality brand! Angel Soft® Professional Series™ is the brand of premium facial tissue that delivers the appearance and softness for today's discerning business customers and employees. Whether you manage a hospitality property, restaurant or an upscale office building, you want to make a positive impression on your guests, patrons or tenants - every time. One of the most simple and fool proof ways to impress people at minimal cost is to offer your customers quality, familiar brands to use in your facilities. Individual Box Dimensions (LxWxH): 9.5" x 4.625" x 2"



Features & Benefits:

- » Premium quality and softness customers will appreciate
- » Clean, upscale design coordinates with Angel Soft ps® bath tissue for an elegant, professional look
- » Includes color indicator sheets signaling the need for refilling
- » A recognized brand by 96% of consumers. (Millward Brown Brand Equity Tracker Q2 2009)
- » Contains at least 10% Post-Consumer Recycled Fiber. Meets or Exceeds EPA Comprehensive Procurement
- » Can help earn LEED credits

Product Details

Brand Owner	GP
Brand	Angel Soft Professional Series®
MFG Part#	48580
Color	White
UP - UPC	073310485805
Each Per Ship Unit	30 Boxes
Items Per Each	100 Sheets
Case Total	3000 Sheets
Sheet (WxL)	7.650" x 8.850"
UNSPSC	14111701
EPA CPG Compliant	Yes
Min. PCW %	10%
Min. Recycled %	10%
LEED O&M	MR, IEQ
Replaces Item	46811/01, 46811
Buy Multiple	6 CS

Case Shipping Info

Case GTIN	10073310485802
Case Gross Wgt	14.000 LBS
Case Net Wgt	8.930 LBS
Case Dimensions (LxWxH)	19.625" x 14.625" x 10.875"
Case Volume	1.806 CFT

Each Shipping Info

Each Gross Weight	0.375 LBS
Each Net Wgt	0.298 LBS
Each Dimensions	9.500" x 4.625" x 2.000"
Each Volume	0.060 CFT

Unit Shipping Info

TI-Qty/Layer	6
HI-Layers/Unit	9
Unit Qty	54
Unit Dimensions (LxWxH)	43.875" x 39.250" x 97.875"

