ergotron® moving you forward

Neo-Flex® Extend LCD Arm

- Features 3-point telescoping motion. Easily position your LCD for the ideal viewing angle and viewing distance
- Compact design frees up desktop space
- Extends LCD out up to 22" (56 cm); push your display out of the way when not in use
- Easy installation and flexibility—install either two or one of the extension arms or just the LCD pivot
- Cable management feature routes cables
 under the arm, out of the way
- Provides premium long-life LCD adjustment while maintaining touch-screen stability
- Allows LCD to be rotated for portrait/ landscape viewing



SLEEK AND DURABLE LCD ARM

Ergotron's Neo-Flex Extend LCD Arm combines value and versatility in a sleek, durable design. Configure as needed to provide ideal viewing angle and viewing distance by installing one or two arm extensions or only the LCD pivot.

Premium long-life LCD adjustment ensures easy positioning of an LCD. Simply extend or retract, tilt the screen 80° up/down, rotate from portrait to landscape or adjust the arm's height – 9.5″ (24 cm) variable height adjustment – on the pole.

- 9.5" (24 cm) variable height adjustment allows arm installation at different heights on pole
- Configuration flexibility: Install one or two arm extensions or only the LCD pivot •
- Lock-out feature can be used to prevent portrait-to-landscape rotation
- Mounting standards: VESA FDMI, MIS-D, 75/100, C (hole patterns = 100x100 mm and 75x75 mm) •
- Mounting options: desk clamp attaches to surface edge 1/2-11/8" (13-48 mm) thick; grommet mount attaches through surface holes $\frac{5}{16}$ - 2" (8–51 mm) wide and up to $2\frac{1}{2}$ " (63 mm) thick
- Durable, easy-to-clean exterior composed of aluminum, high-grade plastic and powder-coated • painted steel



CLAMP AND GROMMET BASES INCLUDED CLAMP TO SURFACES 1/2-17%" (13-48 mm) THICK OR GROMMET MOUNT THROUGH HOLES 5/16-2" (8-51 mm) WIDE, UP TO 21/2" (63 mm) THICK

© Ergotron, Inc. 01.04.2019

Literature made in the U.S.A.

Ergotron devices are not intended to cure, treat, mitigate or prevent any disease.

Patent information available at www.ergotron.com/patents.

Neo-Flex Extend LCD Arm

Part # (color)	45-235-194 (silver)
Includes	Arm, two (2) extensions, LCD energy pivot, desk clamp base, grommet mount base
Typical LCD Size	≤ 24″

LCD SIZE IS APPROXIMATION. DIMENSION IS DIAGONAL MEASUREMENT OF SCREEN. LCD SIZE MAY BE EXCEEDED AS LONG AS SCREEN WEIGHT DOES NOT EXCEED MAXIMUM WEIGHT CAPACITY OF THE MOUNT.

Weight Capacity	7–20 lbs (3,2–9,1 kg)*
Tilt	80°
Pan	360°
Rotation	360°
VESA	MIS-D (75 x 75 – 100 x 100 mm)
Product Weight	8.3 lbs (3,8 kg)
Shipping Weight	9.7 lbs (4,4 kg)
Shipping Dimensions	19.5" x 11.5" x 6.5" (496 x 288 x 164 mm)
Warranty	3 years

 * Monitor depth greater than 2" (5 cm) may diminish capacity



Download additional resources at ergotron.com. For more information: NORTH AMERICA: 800.888.8458 / +1.651.681.7600 / sales@ergotron.com Content subject to change. EMEA: +31.33.45.45.600 / info.eu@ergotron.com

APAC: apaccustomerservice@ergotron.com

OEM: info@oem.ergotron.com



