

Details

LCD60504BLK

TygerClaw Desk
Mount for 13 in.
to 27 in. Monitor



Main Features

- Monitor mounting bracket can hold most 13 in. to 27 in. monitor up to 22 lb.
- Tilt degree from -90 to +90
- Swivel degree up to 180
- Universal mounting pattern with 75 x 75mm and 100 x 100mm
- Free up space and provides a neat and stylish environment to your room
- Constructed with cold steel material to maximize the durability and support
- All necessary mounting hardware is included
- Quick and easy installation
- VESA Compliant, RoHS Compliant



SMOOTH TRANSITION 1.

Bracket tilts -90 to +90° for maximum viewing flexibility

CABLE MANAGEMENT 2.

Keep your cable and accessories organized and neat



STURDY CONSTRUCTION 3.

A solid steel frame that is built to last and keep your TV safe



Technical Specifications

LCD60504BLK

Size	9.9 x 19 x 44.9 cm 3.9 x 7.5 x 17.7 in
Weight	3.2 Kg 7.2 Lb
Type	Monitor Desk Mount
Max Compatible Weight	9.9 Kg 22 Lb
Min / Max Screen Size	13 - 27 in
VESA Compliant	Yes
Tilt Range	-90 to +90 °
Swivel Range	180 °
Integrated Cable Management	Yes
Primary Material	Steel
Max. VESA	100 x 100 mm

