

**Description:**

The TygerClaw pneumatic effortless workstation is a contemporary-styled versatile workstation designed for working with laptops, paper work and presentations. The gas-spring height adjustable mechanism operates with minimal effort - making it great for sit to stand or sharing the workstation with users of various sizes. The smooth writing surface and tablet slot add even more functions. It is perfect for medical, education, hotels, homes, and other work environments. Elegant design with leveling feet that adapt to most uneven floor or surface - keeping everything in place.



Desktop surface	Capacity	Lift	Fit desk depth	Warranty	Additional function
 28"	 17.6	 27.6"-42.9"	 20.6"	 1 Year	 Pneumatic Gas Spring

**Features:**

- Counter-Balance Gas Spring: creates smooth and quick transitions
- Squeeze Lever: makes the adjustment easy
- Stepless Height Settings: for your free height adjustment
- Aluminum Construction: provides a sleek, lighter, and elegant look
- Leveling Feet: adapt to most uneven floor or surface
- Smooth and quiet height adjustment


**Specifications:**

Colour:	BLACK
Materials:	MDF & PVC, Steel, Aluminum, Plastic
Desk Top Size: (Inches)	28" x 19.7" or (710x500mm)
Height Adjustment:	Manual
Desk Top Tilt Range:	N/A
Desk Height Range: (Inches)	27.6"-42.9" or (700-1090mm)
Desk Top Thickness (Inches)	0.59" or (15mm)
Desk Weight Capacity: (lbs)	17.6 lbs or (8kg)
Desk Top Tilt Mechanism:	N/A
Product Dimensions (Inches):	28" x 20.6" x 27.6"-42.9"
Product Weight (lbs):	16.4 lbs
Package Dimensions (Inches):	31.4" x 22.4" x 7.4"
Gross Weight (lbs):	17.6 lbs or (8kg)
Loading QTY (40' HQ):	N/A
Warranty:	1 Year Limited Warranty

**Standards:**
