

Instruction Manual

Customer Service:
US: 1-800-645-2986

Manuel d'instruction

Service à la clientèle
Canada: 888-645-2986

Non-Contact Digital Infrared Forehead Thermometer



Model 695746

⚠ WARNING

Read entire manual before operation. For additional questions or concerns, contact Global Industrial Customer Service at 1-800-645-2986 or visit www.globalindustrial.com.

- Product to be used in ambient temperatures between 60°-95°F (16°-35°C).
- DO NOT use this product in an environment with a relative humidity greater than 93%.
- DO NOT place this product too close to the electromagnetic range, (examples: radio, mobile phone, etc.).
- DO NOT expose to excessive heat or water.
- DO NOT use if product is damaged.
- Sweat, hair, hats, or other foreign matter on the forehead can affect the accuracy of the measurement.
- Ensure the measurement distance is within 1 to 2 inches.
- Contact Global Industrial if there are any problems with the thermometer, DO NOT attempt to do any repairs yourself.
- Keep this manual for future use.

Specifications

Temperature Range:	91.4°-109.4°F (33°-43°C)
Power Supply:	DC 3V - 2 AAA batteries (not included)
Measuring Distance Range:	1-1/6 – 2 in.
Response Time:	1 Second
Memory Data:	20 Records
High-Fever Warning:	5 Beeps
Display:	Blue LCD
Low Battery Alarm:	Yes
Product Weight:	1/4 lb. (excluding batteries)
Product Dimensions:	6.1"L x 3.5"W x 1.7"H
Certification:	FDA
Ambient Temp. Working Range:	60°-95°F (16°-35°C)

Component Identification

- ① LCD Display
- ② Function Button
- ③ “+” Button
- ④ “-” Button
- ⑤ Infrared Sensor
- ⑥ Measurement Trigger
- ⑦ Handle
- ⑧ Battery Cover



Operation Instructions

1. Insert batteries - Open the battery cover and insert (2) AAA batteries (not included) into the bottom of the thermometer. Close the battery cover.
2. The thermometer will beep.
3. Tap the **FUNCTION** button to switch between “body” and “surface” temperature modes.
4. Press the **MEASUREMENT TRIGGER** to measure forehead temperature. In order to get an accurate measurement, ensure the thermometer is 1 to 2 inches away from the forehead.
5. Press “+” or “-” buttons to review the last 20 measurement results.
6. Press and hold the **FUNCTION** button for 3 seconds to access the different function modes below. Tap the **FUNCTION** button again to scroll through the following modes:
 - F1: °F or °C unit mode - Press “+” or “-” button to select.
 - F2: Max. temperature alarm mode; press “+” or “-” button to select.
 - F3: Display data offsetting mode; press “+” or “-” button to select.
 - F4: Buzzer sound activate/deactivate mode; press “+” or “-” button to select.
- Note: Pressing the **MEASUREMENT TRIGGER** button will exit during any set up mode.
7. The thermometer will automatically shut-off when idle and will turn back on by pressing any button.

Product Maintenance

Note: Be sure not to damage and use extra precaution when cleaning the infrared sensor.

- Do not use abrasive cleaners to clean this product.
- Do not submerge the product into water or other liquids.
- Keep the product in a dry place to avoid dust, pollution and direct sunlight.
- Clean regularly using a dry soft cloth. If needed, use a damp cloth with water or a neutral detergent to clean, then wipe dry with a clean cloth.