

# INDUSTRIAL PORTABLE POWER STATION G5000 SERIES

## PORTABLE, INDUSTRIAL, OUTDOOR-RATED

Global Industrial G5000P is designed to meet the diverse power needs of outdoor industrial environments. This robust system boasts rugged construction and advanced weatherproofing technology, ensuring durability and longevity even in harsh conditions. Its portable design allows easy transportation and deployment, enabling you to set up power stations wherever and whenever needed.



### Certifications

UL2743 as Outdoor  
Portable Power and IEC  
60601-1 as Medical  
Equipment



### Rugged, Durable Exoskeleton

Rugged power station  
cabinet with industrial-  
grade metal frame for extra  
protection



### Convenience features for ease of use

Eye hook allows hoist  
connection for lifting and  
moving around job site



### Best-in-class expansion power capability

Patent pending - Supports up  
to 35,840Wh power by  
connecting six G5000E  
expandable batteries



### Heavy-Duty 4-wheel mobility package

10" semi-pneumatic wheels  
with 6" swivel casters for  
smooth movement and  
braking capability



### LED touchscreen with Gorilla Glass

Intuitive, responsive user  
interface shows battery usage  
and other information

# INDUSTRIAL PORTABLE POWER STATION G5000 SERIES

## SPECIFICATIONS:

Model:	812541 - G5000P/ 812542 - G5000E
Inverter Capacity:	5,000W
Peak Surge Power:	10,000W
Battery Capacity:	5,120Wh
Max Battery Expansion:	Up to 35,840 Wh 1 x G5000P + 6 x G5000E
Battery Recharge Time:	80% - 2 hr *AC only 100% - 2.6 hr
Fast Charging:	1.6 hr from 0% to 80% *AC+Solar
Battery Lifecycles:	4,000 cycles up to 10 years with 80 % capacity
Operating Temp.:	14 to 122 °F (-10 to 50°C )
Outdoor Rated:	UL2743
Certification:	ETL, cETL, FCC, DOE, IEC60601-1, N38.3+MSDS
Product Dimension:	G5000P:33.46"x29.53"x36.22" G5000E: 28.74"x22.05"x13.78"
Product Weight:	G5000P: 302.88 lbs; G5000E: 126.57 lbs



## G5000P INTERFACE:



- (3) AC 120V 20A (5-20R GFCI)
- (1) AC 120V 30A (TT-30R)
- (1) AC 120V 30A (L5-30)
- (2) Type-C 100W (4) USBA 18W
- (3) DC 12V 10A
- 7" LED Touchscreen



Connection Cable  
Model 812544  
(Sold separately)

