

Model B2355238



Features:

- **Non-touch measurement**
- **High precision infrared sensor**
- **Practical patent design**
- **High definition LED display**
- **1 second rapid measurement**
- **Stores up to 32 readings**
- **User selectable °F or °C**



Specifications Chart

Temperature Range:	89.6 - 108.4°F (32 - 42.2°C)
Power Source:	2 AAA Batteries (Not Included)
Optimal Measuring Distance:	0.59 - 1.18"
Response Time:	1 Second
Memory Data:	32 Records
Resolution:	0.1°F / 0.1°C
Display:	LED
Alarm:	High/Low Temperature Reading
Product Weight:	0.1 lb. (Excluding Batteries)
Product Dimensions:	1.5"L x 1.5"W x 5.4"H
Accuracy:	±0.3°F (±0.2°C)
Certification:	FDA & CE
Limited Warranty:	1 Year