

Model 2453705



Features:

Reliable Performance

High density foam insulation for rigidity and stable storage temperature

LED Display

LED digital display for clear observation

Adjustable Temperature

Adjustable freezer compartment range: -10°C to -25°C (14°F to -13°F)

Two Alarm Functions

High/low temperature, sensor error

Lockable Design

Door with lock for safety control.

Specifications

Cabinet Type:	Upright
Capacity:	3.2 Cu. Ft.
Temperature Range:	-10 to -25°C (14 to -13°F)
Refrigerant:	R600a
Noise:	27 dBA
Display:	LED
Controller:	Microprocessor
Defrost Mode:	Manual
Power Supply:	115/60 (V/Hz)
Power:	125W
Cooling Type:	Direct Cooling
Exterior Dimensions (WxDxH):	25.2" x 24.0" x 33.9"
Interior Dimensions (WxDxH):	17.1" x 16.1" x 25.0"
Product Weight:	101.4 lbs.
# Shelves:	2
Certifications:	CE; UL/cUL