

## Undercounter Lab Refrigerators:



Model 2453700



Model 2453701



Model 2453702

## Upright Lab Refrigerators:



Model 2453703



Model 2453704

## Undercounter Lab Freezer:



Model 2453705

## Upright Lab Freezer:



Model 2453706

## Ultra-Low Lab Freezer:



Model 2453707

## Specifications:

Model No.:	2453700	2453701	2453702	2453703	2453704	2453705	2453706	2453707
Cabinet Type:	Single Glass Door	Single Glass Door	Single Solid Door	Single Solid Door	Double Glass Door	Single Solid Door	Double Solid Door	Single Solid Door
Capacity:	2.4 Cu. Ft.	4.2 Cu. Ft.	4.2 Cu. Ft.	13.8 Cu. Ft.	31.4 Cu. Ft.	3.2 Cu. Ft.	17.3 Cu. Ft.	3.5 Cu. Ft.
Temperature Range:	2 to 8°C (36 to 46°F)	2 to 8°C (36 to 46°F)	2 to 8°C (36 to 46°F)	2 to 8°C (36 to 46°F)	2 to 8°C (36 to 46°F)	-10 to -25°C (14 to -13°F)	-10 to -30°C (14 to -22°F)	-40 to -86°C (-40 to -122°F)
Refrigerant:	R600a	R600a	R600a	R600a	R600a	R600a	R290	R600a/R1150/R50
Noise:	41 dBA	41 dBA	41 dBA	43 dBA	43 dBA	27 dBA	43 dBA	46.8 dBA
Display:	LED	LED	LED	LED	LED	LED	LED	LED
Controller:	Microprocessor	Microprocessor	Microprocessor	Microprocessor	Microprocessor	Microprocessor	Microprocessor	Microprocessor
Defrost Mode:	Auto	Auto	Auto	Auto	Auto	Manual	Manual	Manual
Power Supply:	115/60 (V/Hz)	115/60 (V/Hz)	115/60 (V/Hz)	115/60 (V/Hz)	115/60 (V/Hz)	115/60 (V/Hz)	115/60 (V/Hz)	120/60 (V/Hz)
Power:	150W	230W	190W	240W	850W	125W	600W	680W
Electrical Current:	1.7A	1.5A	1.4A	2.4A	7.5A	3.5A	5.4A	6.5A
Cooling Type:	Forced Air Cooling	Forced Air Cooling	Forced Air Cooling	Forced Air Cooling	Forced Air Cooling	Direct Cooling	Direct Cooling	Direct Cooling
Exterior (LxWxH):	19.5" x 22.8" x 26.0"	23.5" x 25.0" x 31.9"	23.5" x 25.0" x 31.9"	26.2" x 28.0" x 77.4"	44.5" x 29.7" x 78.0"	25.2" x 24.0" x 33.9"	36.0" x 31.9" x 73.2"	30" x 26" x 32"
Interior (LxWxH):	16.3" x 15.2" x 19.9"	20.3" x 16.3" x 24.8"	20.3" x 16.3" x 24.8"	20.9" x 21.9" x 54.3"	40.6" x 23.2" x 56.1"	17.1" x 16.1" x 25.0"	27.0" x 24.0" x 48.3"	13" x 19" x 25"
Product Weight:	83.8 lbs.	101.5 lbs.	90.5 lbs.	255.8 lbs.	500.4 lbs.	101.4 lbs.	361.6 lbs.	238 lbs.
# Shelves/Baskets:	2/1	3/1	3/1	7/0	12/0	2/0	10/0	1/2
Certifications:	CE; UL/cUL	CE; UL/cUL	CE; UL/cUL	CE; UL/cUL	CE; UL/cUL	CE; UL/cUL	CE; UL/cUL	CE; UL/cUL