

Specifications

Model 2453707



Features:

- **Ultra-Low Temperature of -40° to -86°C**
- **Energy Efficient, Safe and Reliable**
- **Ergonomic Design**
- **Low Noise**
- **Superior Thermal Insulation**
- **Security Door Lock**
- **USB Data Storage; capable of storing more than 15 years of data**
- **LED Display**
- **9 Alarm Functions:**

High/low temperature, sensor error, power failure, remote alarm, hot condenser, high/low voltage, low battery, high ambient temperature, door ajar.

Specifications

Cabinet Type:	Upright
Capacity:	3.5 Cu. Ft.
Temperature Range:	-40 to -86°C (-40 to -122°F)
Refrigerant:	R600a/R1150/R50
Noise:	46.8 dBA
Display:	LED
Controller:	Microprocessor
Defrost Mode:	Manual
Power Supply:	120/60 (V/Hz)
Power:	680W
Electrical Current:	6.5A
Cooling Type:	Direct Cooling
Exterior Dimensions (WxDxH):	30" x 26" x 32"
Interior Dimensions (WxDxH):	13" x 19" x 25"
Product Weight:	238 lbs.
# Shelves/Inner Doors:	1/2
Certifications:	CE; UL/cUL