

POLYOLEFIN SHRINK FILM

FILM & BAGS

Best value for general purpose shrink applications

- High clarity – co-extruded, multi-layered construction
- Meets FDA specifications for direct food contact
- Softer than PVC film, yet strong and highly tear resistant
- “Smoke-Free”
- Runs on a variety of equipment

POF CF shrink film is a multi-purpose centerfold shrink film for products including fresh food. It is strong and flexible, but softer than PVC film. POF film is also highly tear resistant with superior optical properties. The film has an excellent gloss and sparkle with low haze and crystal clear clarity for enhanced appearance and product appeal. POF film is very versatile and can be used with virtually any shrink machine. It is “smoke free” and meets FDA specifications for direct food contact. The film has a high burnout resistance so there are no deposits on sealing wires. The strong skintight film extends the shelf life of products and also protects these products from dust, moisture, and oil damage. Moreover, the film will protect from pilfering as it provides a tamper proof package. Our POF film shrinks best between 300°F-338°F (150-170° C) with MD and TD of 60%. MD (machine direction) is vertical or length shrinkage. TD (transverse direction) is horizontal or width shrinkage.



Stock #	Size	Thickness	Length (ft)	Weight
O-12-75-500	12"	75	500	4
O-10-75-3500	10"	75	3,500	25
O-12-75-3500	12"	75	3,500	29
O-14-75-3500	14"	75	3,500	33
O-16-75-3500	16"	75	3,500	37
O-18-75-3500	18"	75	3,500	37
O-22-75-3500	22"	75	3,500	50
O-24-75-3500	24"	75	3,500	55

POF shrink bags are convenient for quick and easy shrink wrapping. Speed up your packaging operations. Produce crystal clear packages in seconds. Ideal for archival packaging. Available in 75 gauge, 500pcs/box (A) or 250pcs/box (B).

Stock #	Size	Thickness	#/Case	Weight
OSB-4-6-75A	4" x 6"	75	500	1
OSB-6-6.5-75A	6" x 6.5"	75	500	2
OSB-6.5-10.5-75A	6.5" x 10.5"	75	500	3
OSB-8-12-75A	8" x 12"	75	500	3
OSB-12-16-75A	12" x 16"	75	500	3

