

SAFETY DATA SHEET

1. Identification

Product identifier	Georgia-Pacific® Heavy Duty Industrial Hand Cleaner		
Product list	Georgia-Pacific® Heavy Duty Industrial Hand Cleaner (3L) SKU 44627 Georgia-Pacific® Heavy Duty Industrial Hand Cleaner (1.5L) SKU 44629 Georgia-Pacific® Heavy Duty Industrial Hand Cleaner (1.5L) GP6254 Georgia-Pacific® Heavy Duty Industrial Hand Cleaner (100mL) GP6292		
Other means of identification	None.		
Recommended use	Heavy duty hand cleaner designed for tough industrial soils such as tar, paint, lacquer and other difficult cleaning tasks.		
Recommended restrictions	None known.		
Manufacturer/Importer/Supplier/Distributor information			
Company name	Manufactured for:		
Address	Georgia-Pacific Consumer Products LP 133 Peachtree Street, NE Atlanta, GA 30303		
Telephone	Technical Information:	866.435.5647	
	SDS Request:	404.652.5119	
E-mail	MSDSREQ@GAPAC.com		
Emergency phone number	Chemtrec - Emergency:	800.424.9300	

2. Hazard(s) identification

Physical hazards	Not classified.		
Health hazards	Eye irritation		Category 2B
Environmental hazards	Hazardous to the aquatic environment, acute hazard		Category 3
OSHA defined hazards	Not classified.		
Label elements			
Hazard symbol	None.		
Signal word	Warning		
Hazard statement	Causes eye irritation. Harmful to aquatic life.		
Precautionary statement			
Prevention	Wash thoroughly after handling large quantities. Avoid release to the environment.		
Response	If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.		
Storage	Store away from incompatible materials.		
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.		
Hazard(s) not otherwise classified (HNOC)	None known.		
Supplemental information	None.		

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
DECETH-6		26183-52-8	7 - 13
AMORPHOUS SILICA		112926-00-8	3 - 7
GLYCERIN		56-81-5	1 - 5
OLEIC ACID		67701-08-0	0.5 - 1.5
D-LIMONENE		5989-27-5	0.1 - 1
Other components below reportable levels			65 - 85

4. First-aid measures

Inhalation	Not a normal route of exposure. If symptoms develop, remove to fresh air. Get medical attention if irritation persists.
Skin contact	If irritation occurs, flush skin with plenty of water. Seek medical attention if irritation persists.
Eye contact	Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	Rinse mouth. Do not induce vomiting without advice from poison control center. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Causes eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Powder, water spray, foam, carbon dioxide.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Firefighters should wear full protective clothing including self contained breathing apparatus.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	This product is not expected to burn unless all water is boiled away. The remaining organic compounds may be ignitable. Use water to cool containers exposed to fire.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Use personal protection recommended in Section 8. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. Spills of this material are a slipping hazard.
Methods and materials for containment and cleaning up	Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Prevent product from entering drains. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid release to the environment. If large quantities enter a waterway, advise local authorities.

7. Handling and storage

Precautions for safe handling	For external use only. Keep out of the reach of children. Do not get this material in contact with eyes. Wear gloves and safety glasses or goggles if handling large quantities. Avoid prolonged exposure. Provide adequate ventilation. Avoid release to the environment.
Conditions for safe storage, including any incompatibilities	Store in original tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
GLYCERIN (CAS 56-81-5)	PEL	5 mg/m ³	Respirable fraction.
		15 mg/m ³	Total dust.

US. OSHA Table Z-3 (29 CFR 1910.1000)

Components	Type	Value
AMORPHOUS SILICA (CAS 112926-00-8)	TWA	13.3 mg/m ³

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
AMORPHOUS SILICA (CAS 112926-00-8)	TWA	6 mg/m ³

Biological limit values No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls General ventilation normally adequate.

Individual protection measures, such as personal protective equipment

Eye/face protection None necessary under normal conditions of use. Wear safety glasses or goggles if handling large quantities.

Skin protection

Hand protection None necessary under normal conditions of use. Wear appropriate gloves if handling large quantities.

Other

None necessary under normal conditions of use.

Respiratory protection Under normal conditions of use respiratory protection is not expected to be required.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

9. Physical and chemical properties

Appearance Hand cleanser containing scrubbing agents.

Physical state Liquid.

Form Liquid gel.

Color Yellow.

Odor Citrus.

Odor threshold Not available.

pH 6 - 7

Melting point/freezing point Not available.

Initial boiling point and boiling range Not available.

Flash point Not available.

Evaporation rate Not available.

Flammability (solid, gas) Not applicable.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Explosive limit - lower (%) Not available.

Explosive limit - upper (%) Not available.

Vapor pressure Not available.

Vapor density Not available.

Relative density Not available.

Solubility(ies)

Solubility (water) Not available.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not available.

Decomposition temperature Not available.

Viscosity Not available.

10. Stability and reactivity

Reactivity Heat. Incompatible materials.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.

Conditions to avoid Contact with incompatible materials.

Incompatible materials Strong oxidizing agents.

Hazardous decomposition products Small amounts of nitrogen oxides, carbon monoxide and carbon dioxide may be released.

11. Toxicological information

Information on likely routes of exposure

Inhalation No effects expected under normal conditions of use.

Skin contact No effects expected under normal conditions of use. Prolonged skin contact may cause temporary irritation.

Eye contact Causes eye irritation.

Ingestion Not applicable under normal conditions of use. May cause gastrointestinal irritation if ingested.

Symptoms related to the physical, chemical and toxicological characteristics Causes eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity Not known.

Components	Species	Test Results
------------	---------	--------------

AMORPHOUS SILICA (CAS 112926-00-8)

Acute

Dermal

LD50	Rabbit	> 5000 mg/kg
------	--------	--------------

Oral

LD50	Rat	> 5000 mg/kg
------	-----	--------------

D-LIMONENE (CAS 5989-27-5)

Acute

Oral

LD50	Mouse	5600 - 6600 mg/kg
------	-------	-------------------

GLYCERIN (CAS 56-81-5)

Acute

Dermal

	Rabbit	> 5000 mg/kg
--	--------	--------------

Oral

	Rat	> 5000 mg/kg
--	-----	--------------

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation Causes eye irritation.

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization This product is not expected to cause skin sensitization.

Germ cell mutagenicity Not hazardous under normal conditions of use.

Carcinogenicity Not classified.

IARC Monographs. Overall Evaluation of Carcinogenicity

AMORPHOUS SILICA (CAS 112926-00-8)

3 Not classifiable as to carcinogenicity to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not an aspiration hazard.
Chronic effects	Not hazardous under normal conditions of use.

12. Ecological information

Ecotoxicity Harmful to aquatic life.

Product		Species	Test Results
Georgia-Pacific® Heavy Duty Industrial Hand Cleaner			
Aquatic			
Crustacea	EC50	Daphnia	11091.3926 mg/L, 48 Hours estimated
<i>Acute</i>			
Fish	LC50	Fish	123.8493 mg/l, 96 hours estimated
Components		Species	Test Results
D-LIMONENE (CAS 5989-27-5)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia pulex)	69.6 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	0.619 - 0.796 mg/l, 96 hours
GLYCERIN (CAS 56-81-5)			
Aquatic			
Fish	LC50	Fish	> 100 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

D-LIMONENE	4.232
GLYCERIN	-1.76

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	This product, if discarded, is not considered a hazardous waste under Federal Hazardous Waste Regulations 40 CFR 261. If processing, use, or contamination alters the material, the waste must be tested using methods described in 40 CFR 261 to determine if it meets applicable definitions of hazardous wastes.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty packaging/container can be disposed in accordance with all applicable regulations.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

15. Regulatory information

US federal regulations SDS prepared pursuant to the Hazard Communication Standard (29 CFR 1910.1200). This product is regulated under the US Federal Food, Drug, and Cosmetic Act.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

Classified hazard categories Serious eye damage or eye irritation

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

California Proposition 65



WARNING: California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This product does not require warning.

16. Other information, including date of preparation or last revision

Issue date July-27-2017
Revision date May-15-2018
Version # 02
HMIS® ratings Health: 1
Flammability: 0
Physical hazard: 0
NFPA ratings Health: 1
Flammability: 0
Instability: 0

Disclaimer

This SDS is intended to quickly provide useful information to the user(s) of this material or product. It is not intended to serve as a comprehensive discussion of all possible risks or hazards, and it assumes a reasonable use of the product. The information contained in this SDS is believed to be accurate as of the date of preparation of this SDS and has been compiled from sources believed to be reliable. It is offered for your consideration, investigation and verification. The user or handler (or their employer) should consider the specific conditions in which this material will be used, handled, or stored and determine what specific safety or other precautions are required. Employers should ensure that their employees, agents, contractors, and customers who will use the product receive adequate warnings and safe handling procedures, including a current SDS. Product users or handlers (or their employer) who are unsure of what specific precautions are required should consult their employer, product supplier, or safety or health professionals before handling or working with this product. Please notify us immediately if you believe this SDS or other safety and health information about this product is inaccurate or incomplete.

Revision information

Product and Company Identification: Product Codes